

nVent CADDY Cat CR50 Low-Voltage Cable Retainer, 50 mm dia



CATALOG NUMBER

CATCR50

FEATURES

Complies with the NEC®, the CEC and TIA standards for cable management

Allows for horizontal and vertical change of direction

Installs easily

Works with CAT 5e and higher, fibre optic and coaxial cable

Residential application

Suitable for air handling spaces (plenum)



PRODUCT ATTRIBUTES

Article Number: 182335

Material: Polypropylene


Diameter (Ø): 50 mm

Area: 68mm²

Cable Capacity, Cat 5e: 50

Cable Capacity, Cat 6: 36

Static Load: 45N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

