


# Grub Screw



Zero external envelope. Enables axial or radial positioning rather than clamping. Ideal for torque transmission.

## FEATURES

For mounting threaded insert and perforated strip at horizontal rail

Slotted head requires flat-bladed screwdriver that enhances rotational leverage and simplify the installation process for fasteners

Torx imprint bears greater torque

The Torx star-shaped head prevents cam-out

**Product Type:** Screw  
**Type:** Grub Screw



## SPECIFICATIONS

Table 1/2

| Catalog Number | Length | Package Quantity | Thread Size | Finish        | Material        | Product Family                                                              |
|----------------|--------|------------------|-------------|---------------|-----------------|-----------------------------------------------------------------------------|
| 21100-276      | 8mm    | 100              | M2.5        | Nickel Plated | Steel           | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO |
| 21100-646      | 8mm    | 100              | M3          | Nickel Plated | Steel           | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO |
| 21102-980      | 8mm    | 100              | M2.5        |               | Stainless Steel |                                                                             |

Table 2/2

| Catalog Number | Works With               | Thread Length | Torque  | Certifications |
|----------------|--------------------------|---------------|---------|----------------|
| 21100-276      | Subracks, Cases, Chassis | 8mm           | 0.3N·m  | RoHS           |
| 21100-646      | Subracks, Cases, Chassis | 8mm           | 0.45N·m | RoHS           |
| 21102-980      | Subracks, Cases, Chassis | 8mm           | 0.3N·m  |                |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

