

Branch Line Restraint Structure Attachment to Wood/Concrete, M10, M12 Rod

CATALOG NUMBER

CSBBRS2MEG

FEATURES

Swivel barrel nut accepts 3/8" or 1/2" (M10 or M12) threaded rod

Attaches to wood or concrete where cracked concrete approval is not needed



PRODUCT ATTRIBUTES

Article Number: 402240

Material: Steel

Finish: Electrogalvanized

Rod Size (RS): 10;12

Height (H): 28.2 mm

Length (L): 40.4mm

Width (W): 26.9 mm


Screw Diameter (Sc): 1/4"

Screw Length (L): 44.5mm

Drill Bit Diameter: 5mm

ADDITIONAL PRODUCT DETAILS

Branch line structural attachments are for restraint only and not for the hanging of fire sprinkler piping.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

