

# Cable Clamp, 3–13 mm dia



## CATALOG NUMBER

**SCDKS313**

## FEATURES

For installation of single or multiple cables directly against concrete surface

Discrete low-profile clamp reduces visual impact

Halogen free

UV-stabilized

## PRODUCT ATTRIBUTES

Article Number: 800050

Material: Polypropylene


Temperature: -10 to 85 °C

Diameter (Ø): 3 - 13 mm

Drill Hole Diameter: 6mm

Drill Hole Depth: 30mm

Static Load: 170N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

