

PEMSA Wire Basket Tray C Bracket, 265 mm



CATALOG NUMBER

WBT200CBRKT

FEATURES

Easy to use, quick connect feature

Ideal for ceiling, wall and channel installations

Side load access for cable installation

IEC 61537 load rating and earthing compliant



PRODUCT ATTRIBUTES

Article Number: 820330

Material: Steel

Finish: Electrogalvanized

Length 1 (L1): 137 mm

Length 2 (L2): 265 mm

Width (W): 54 mm

Height (H): 190 mm

Static Load: 284N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

