

# nVent CADDY Speed Link LD Locking Device



## FEATURES

Low-profile locking device minimizes visual impact


Suitable for 1.5 mm nVent CADDY Speed Link cable

## SPECIFICATIONS

| Catalog Number | Article Number | Material                        | Wire Rope Diameter | Height (H) | Width (W) |
|----------------|----------------|---------------------------------|--------------------|------------|-----------|
| SLJR200        | 196008         | Stainless Steel 304 (EN 1.4301) | 1.5 mm             | 19 mm      | 12.7 mm   |

## ADDITIONAL PRODUCT DETAILS

The 1.5 mm locking devices are only to be used with the SLC15L1000SP and SLC15L50MSP wire spools, or any other 1.5 mm nVent CADDY Speed Link accessories. Do not use with any other wires.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

