


# Vertical Adjustable Coupler



## FEATURES

Provides high-strength joint with SPEEDWAY Cable Ladder profile

Integral hinge allows simple vertical cable ladder joint adjustments


Installs quickly and easily with included hardware

Multiple slots allow for field adjustments



## SPECIFICATIONS

| Catalog Number | Article Number | Material | Finish             | Angle (a) | A      | B     | C    |
|----------------|----------------|----------|--------------------|-----------|--------|-------|------|
| CLSW4VACGA     | 842030         | Steel    | Hot-Dip Galvanized | 0 - 90 °  | 150 mm | 62 mm | 2 mm |



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

