


Guide Rail Multi Piece, Mid-Piece Aluminium/Plastic Extrusion



Guide rail mid-piece for individual multi-piece guide rails out of plastic or Aluminum extrusion. Suitable for Standard, Accessory, 4.4" PCB types and end pieces with coding.

FEATURES

Middle profile for mounting guide rails for 2 mm groove width

2 plastic end pieces are required; these are pushed on to both ends of the middle profile

Guide rails can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Storage temperature: from -40 °C ... 130 °C

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Product Type: Guide Rail
Type: Middle Section



SPECIFICATIONS

Table 1/2

Catalog Number	Board Depth	Groove Width	Color	Material	Package Quantity	Works With
34560-891	160mm	2	Silver	Aluminum	1	Subracks, Cases, Chassis
34560-892	220mm	2	Silver	Aluminum	1	Subracks, Cases, Chassis
34560-893	280mm	2	Silver	Aluminum	1	Subracks, Cases, Chassis
34560-900	1000mm	2	Silver	Aluminum	1	Subracks, Cases, Chassis
34564-891	160mm	2	Grey	PVC	1	Subracks, Cases, Chassis
34564-892	220mm	2	Grey	PVC	1	Subracks, Cases, Chassis
34564-893	280mm	2	Grey	PVC	1	Subracks, Cases, Chassis
34564-900	1000mm	2	Grey	PVC	1	Subracks, Cases, Chassis

Table 2/2

Catalog Number	Finish	Color Code
34560-891	Anodized	

Catalog Number	Finish	Color Code
34560-892	Anodized	
34560-893	Anodized	
34560-900	Anodized	
34564-891		RAL 7035
34564-892		RAL 7035
34564-893		RAL 7035
34564-900		RAL 7035

ADDITIONAL PRODUCT DETAILS

Delivery may be in Standard Pack Quantity (SPQ). Pricing is per individual item.

One guide rail consists of 1 pair of head pieces and 1 profile piece.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

