

# Wire Basket Tray Bar Splice



The nVent CADDY Wire Basket Tray Bar Splice offers a versatile solution for straight sections and fittings within shaped wire basket tray systems. Engineered for structural continuity, the Bar Splice delivers enhanced support between tray runs. With a slotted design, contractors can create innovative field configurations—ideal for forming reducers or achieving precise angles. Whether you're adapting tray geometry or reinforcing connections, the Bar Splice ensures a clean, secure fit with finishes that match your installation.

## FEATURES

Multiple color options to coordinate with cable tray selection

Creates additional support for cable tray runs

Optimal for angles 30 degrees and smaller


**Material:** Steel  
**Finish:** Electrogalvanized



## SPECIFICATIONS

| Catalog Number  | Color | Height (H) | Width (W) | Length (L) | Unit Weight | Certifications                              |
|-----------------|-------|------------|-----------|------------|-------------|---------------------------------------------|
| WBTBSPLICE      |       | 17.46 mm   | 4.55 mm   | 304.8mm    | 0.127 kg    |                                             |
| WBTBSPLICEBA    | Black | 17.46 mm   | 4.55 mm   | 304.8mm    | 0.127 kg    |                                             |
| WBTBSPLICEKIT   |       | 17.46 mm   | 4.55 mm   | 304.8mm    | 0.127 kg    | CE, nVent CADDY Wire Basket Tray System, UL |
| WBTBSPLICEKITBA | Black | 17.46 mm   | 4.55 mm   | 304.8mm    | 0.127 kg    | CE, nVent CADDY Wire Basket Tray System, UL |
| WBTBSPLICEKITWH | White | 17.46 mm   | 4.55 mm   | 304.8mm    | 0.127 kg    |                                             |
| WBTBSPLICEWH    | White | 17.46 mm   | 4.55 mm   | 304.8mm    | 0.127 kg    |                                             |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

