

Cat HP J-Hook Mod Clip for M4-M12 Threaded Rod, 4,8 - 6,4mm Wire



CATALOG NUMBER

CATHPM4Z34

Improved nVent CADDY Cat HP Mod Clip J-Hook with Rod/Wire Clip allows for quick attachment to threaded rod or wire without screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

FEATURES

Tool-free assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY



PRODUCT ATTRIBUTES

Article Number: 186082


Finish: nVent CADDY Armour

Material: Spring Steel

Rod Size (RS): M4;M6;M8;M10;M12

Wire Size: 4.8 - 6.4 mm

Static Load: 130N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

