

# PX Heavy Duty Pipe Clamp with External Thread



## FEATURES

Includes male/female combination nut

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

Temperature: -50 to 120 °C

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material                                         | Finish            | Outer Diameter (OD) | NB/D N | Rod Size (RS) |
|----------------|----------------|--------------------------------------------------|-------------------|---------------------|--------|---------------|
| PXI013S6       | 578250         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 10 - 13 mm          |        | M10           |
| PXI018EG       | 577870         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 14 - 18 mm          | 10     | M10           |
| PXI018S6       | 578260         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 14 - 18 mm          | 10     | M10           |
| PXI022EG       | 577880         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 19 - 22 mm          | 15     | M10           |
| PXI022S6       | 578270         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 19 - 22 mm          | 15     | M10           |
| PXI028EG       | 577890         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 23 - 28 mm          | 20     | M10           |
| PXI028S6       | 578280         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 23 - 28 mm          | 20     | M10           |

| Catalog Number | Article Number | Material                                         | Finish            | Outer Diameter (OD) | NB/D N | Rod Size (RS) |
|----------------|----------------|--------------------------------------------------|-------------------|---------------------|--------|---------------|
| PXI034EG       | 577900         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 29 - 34 mm          | 25     | M10           |
| PXI034S6       | 578290         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 29 - 34 mm          | 25     | M10           |
| PXI045EG       | 577920         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 41 - 45 mm          | 32     | M10           |
| PXI045S6       | 578310         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 41 - 45 mm          | 32     | M10           |
| PXI050EG       | 577930         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 46 - 50 mm          | 40     | M10           |
| PXI050S6       | 578320         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 46 - 50 mm          | 40     | M10           |
| PXI061EG       | 577950         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 56 - 61 mm          | 50     | M10           |
| PXI061S6       | 578340         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 56 - 61 mm          | 50     | M10           |
| PXI081EG       | 577980         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 75 - 81 mm          | 65     | M10           |
| PXI081S6       | 578370         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 75 - 81 mm          | 65     | M10           |
| PXI093EG       | 578000         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 88 - 93 mm          | 80     | M10           |
| PXI093S6       | 578390         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 88 - 93 mm          | 80     | M10           |
| PXI099S6       | 578400         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 94 - 99 mm          |        | M10           |

Table 2/2

| Catalog Number | Article Number | Material                                         | Finish            | Outer Diameter (OD) | NB/D N | Rod Size (RS) |
|----------------|----------------|--------------------------------------------------|-------------------|---------------------|--------|---------------|
| PXI105S6       | 578410         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 100 - 105 mm        |        | M10           |
| PXI111S6       | 578420         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 106 - 111 mm        |        | M10           |
| PXI118EG       | 578040         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 112 - 118 mm        | 100    | M10           |
| PXI118S6       | 578430         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 112 - 118 mm        | 100    | M10           |
| PXI125S6       | 578440         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 119 - 125 mm        |        | M12           |

| Catalog Number | Article Number | Material                                         | Finish            | Outer Diameter (OD) | NB/D N | Rod Size (RS) |
|----------------|----------------|--------------------------------------------------|-------------------|---------------------|--------|---------------|
| PXI145EG       | 578080         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 139 - 145 mm        | 125    | M12           |
| PXI145S6       | 578470         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 139 - 145 mm        | 125    | M12           |
| PXI151S6       | 578480         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 146 - 151 mm        |        | M12           |
| PXI164S6       | 578500         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 158 - 164 mm        |        | M12           |
| PXI170EG       | 578120         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 165 - 170 mm        | 150    | M12           |
| PXI170S6       | 578510         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 165 - 170 mm        | 150    | M12           |
| PXI194S6       | 578540         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 188 - 194 mm        |        | M12           |
| PXI220EG       | 578180         | Steel, EPDM-SBR Rubber                           | Electrogalvanized | 215 - 220 mm        | 200    | M12           |
| PXI220S6       | 578570         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 215 - 220 mm        | 200    | M12           |
| PXI040S6       | 578300         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 35 - 40 mm          |        | M10           |
| PXI055S6       | 578330         | Stainless Steel 316 (EN 1.4401), EPDM-SBR Rubber |                   | 51 - 55 mm          |        | M10           |

Table 1/2

| Catalog Number | Article Number | Gewinde (G) | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Length (L) | Static Load |
|----------------|----------------|-------------|-----------|---------------|---------------------|------------------|-------------|
| PXI013S6       | 578250         | 1/2"        | 27 mm     | 2 mm          | 6                   | 20mm             | 2500N       |
| PXI018EG       | 577870         | 1/2"        | 27 mm     | 2.3 mm        | 6                   | 20mm             | 2500N       |
| PXI018S6       | 578260         | 1/2"        | 27 mm     | 2 mm          | 6                   | 20mm             | 2500N       |
| PXI022EG       | 577880         | 1/2"        | 27 mm     | 2.3 mm        | 6                   | 20mm             | 2500N       |
| PXI022S6       | 578270         | 1/2"        | 27 mm     | 2 mm          | 6                   | 20mm             | 2500N       |
| PXI028EG       | 577890         | 1/2"        | 27 mm     | 2.3 mm        | 6                   | 20mm             | 2500N       |
| PXI028S6       | 578280         | 1/2"        | 27 mm     | 2 mm          | 6                   | 20mm             | 2500N       |
| PXI034EG       | 577900         | 1/2"        | 27 mm     | 2.3 mm        | 6                   | 20mm             | 2500N       |
| PXI034S6       | 578290         | 1/2"        | 27 mm     | 2 mm          | 6                   | 20mm             | 2500N       |
| PXI045EG       | 577920         | 1/2"        | 27 mm     | 2.3 mm        | 6                   | 20mm             | 2500N       |
| PXI045S6       | 578310         | 1/2"        | 27 mm     | 2 mm          | 6                   | 20mm             | 2500N       |
| PXI050EG       | 577930         | 1/2"        | 27 mm     | 2.3 mm        | 6                   | 20mm             | 2500N       |


| Catalog Number | Article Number | Gewinde (G) | Width(W) | Thickness (T) | Screw Diameter (Sc) | Screw Length (L) | Static Load |
|----------------|----------------|-------------|----------|---------------|---------------------|------------------|-------------|
| PXI050S6       | 578320         | 1/2"        | 27 mm    | 2 mm          | 6                   | 20mm             | 2500N       |
| PXI061EG       | 577950         | 1/2"        | 31 mm    | 2.5 mm        | 8                   | 25mm             | 2500N       |
| PXI061S6       | 578340         | 1/2"        | 31 mm    | 2 mm          | 8                   | 25mm             | 2500N       |
| PXI081EG       | 577980         | 1/2"        | 31 mm    | 2.5 mm        | 8                   | 25mm             | 2500N       |
| PXI081S6       | 578370         | 1/2"        | 31 mm    | 2 mm          | 8                   | 25mm             | 2500N       |
| PXI093EG       | 578000         | 1/2"        | 31 mm    | 2.5 mm        | 8                   | 25mm             | 2500N       |
| PXI093S6       | 578390         | 1/2"        | 31 mm    | 2 mm          | 8                   | 25mm             | 2500N       |
| PXI099S6       | 578400         | 1/2"        | 31 mm    | 2 mm          | 8                   | 25mm             | 2500N       |

Table 2/2

| Catalog Number | Article Number | Gewinde (G) | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Length (L) | Static Load |
|----------------|----------------|-------------|-----------|---------------|---------------------|------------------|-------------|
| PXI105S6       | 578410         | 1/2"        | 31 mm     | 2 mm          | 8                   | 25mm             | 2500N       |
| PXI111S6       | 578420         | 1/2"        | 31 mm     | 2 mm          | 8                   | 25mm             | 2500N       |
| PXI118EG       | 578040         | 1/2"        | 31 mm     | 2.5 mm        | 8                   | 25mm             | 2500N       |
| PXI118S6       | 578430         | 1/2"        | 31 mm     | 2 mm          | 8                   | 25mm             | 2500N       |
| PXI125S6       | 578440         | 3/4"        | 38 mm     | 2.5 mm        | 8                   | 30mm             | 3500N       |
| PXI145EG       | 578080         | 3/4"        | 38 mm     | 2.9 mm        | 8                   | 30mm             | 3500N       |
| PXI145S6       | 578470         | 3/4"        | 38 mm     | 2.5 mm        | 8                   | 30mm             | 3500N       |
| PXI151S6       | 578480         | 3/4"        | 38 mm     | 2.5 mm        | 8                   | 30mm             | 3500N       |
| PXI164S6       | 578500         | 3/4"        | 38 mm     | 2.5 mm        | 8                   | 30mm             | 3500N       |
| PXI170EG       | 578120         | 3/4"        | 38 mm     | 2.9 mm        | 8                   | 30mm             | 3500N       |
| PXI170S6       | 578510         | 3/4"        | 38 mm     | 2.5 mm        | 8                   | 30mm             | 3500N       |
| PXI194S6       | 578540         | 3/4"        | 38 mm     | 2.5 mm        | 8                   | 30mm             | 3500N       |
| PXI220EG       | 578180         | 3/4"        | 38 mm     | 2.9 mm        | 8                   | 30mm             | 3500N       |
| PXI220S6       | 578570         | 3/4"        | 38 mm     | 2.5 mm        | 8                   | 30mm             | 3500N       |
| PXI040S6       | 578300         | 1/2"        | 27 mm     | 2 mm          | 6                   | 20mm             | 2500N       |
| PXI055S6       | 578330         | 1/2"        | 27 mm     | 2 mm          | 6                   | 20mm             | 2500N       |

## ADDITIONAL PRODUCT DETAILS

Lining is EPDM rubber.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

