

Wire Basket Tray Center Support



The nVent CADDY Wire Basket Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FEATURES

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY Wire Basket Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod

Material: Steel



SPECIFICATIONS

Table 1/2


Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)
WBTCTSPRT12	Electrogalvanized		193.55 mm	41.4 mm	292.176mm	15.75 mm
WBTCTSPRT12WH	Electrogalvanized	White	193.55 mm	41.4 mm	292.176mm	15.75 mm
WBTCTSPRT16WH	Pregalvanized	White	193.55 mm	41.4 mm	392.201mm	15.75 mm
WBTCTSPRT18	Pregalvanized		193.55 mm	41.4 mm	442.214mm	15.75 mm
WBTCTSPRT4	Electrogalvanized		193.55 mm	41.4 mm	105.156mm	15.75 mm
WBTCTSPRT4BA	Electrogalvanized	Black	193.55 mm	41.4 mm	105.156mm	15.75 mm
WBTCTSPRT4WH	Electrogalvanized	White	193.55 mm	41.4 mm	105.156mm	15.75 mm

Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)
WBTCTSPRT6	Electrogalvanized		193.55 mm	41.4 mm	147.777mm	15.75 mm
WBTCTSPRT6WH	Electrogalvanized	White	193.55 mm	41.4 mm	147.777mm	15.75 mm
WBTCTSPRT8	Electrogalvanized		193.55 mm	41.4 mm	190.551mm	15.75 mm
WBTCTSPRT8WH	Electrogalvanized	White	193.55 mm	41.4 mm	190.551mm	15.75 mm
WBTCTSPRT16BA	Pregalvanized	Black	193.55 mm	41.4 mm	392.201mm	15.75 mm
WBTCTSPRT18WH	Pregalvanized	White	193.55 mm	41.4 mm	442.214mm	15.75 mm
WBTCTSPRT20BA	Pregalvanized	Black	193.55 mm	41.4 mm	492.227mm	15.75 mm
WBTCTSPRT24	Pregalvanized		193.55 mm	41.4 mm	592.252mm	15.75 mm
WBTCTSPRT24BA	Pregalvanized	Black	193.55 mm	41.4 mm	592.252mm	15.75 mm
WBTCTSPRT24WH	Pregalvanized	White	193.55 mm	41.4 mm	592.252mm	15.75 mm

Table 2/2

Catalog Number	Unit Weight	Certifications
WBTCTSPRT12	1.225 kg	CE, nVent CADDY Wire Basket Tray System
WBTCTSPRT12WH	1.225 kg	
WBTCTSPRT16WH	1.497 kg	
WBTCTSPRT18	1.542 kg	
WBTCTSPRT4	0.7 kg	CE, nVent CADDY Wire Basket Tray System
WBTCTSPRT4BA	0.7 kg	CE, nVent CADDY Wire Basket Tray System
WBTCTSPRT4WH	0.7 kg	
WBTCTSPRT6	0.816 kg	CE, nVent CADDY Wire Basket Tray System
WBTCTSPRT6WH	0.816 kg	
WBTCTSPRT8	0.907 kg	CE, nVent CADDY Wire Basket Tray System
WBTCTSPRT8WH	0.907 kg	
WBTCTSPRT16BA	1.497 kg	
WBTCTSPRT18WH	1.542 kg	
WBTCTSPRT20BA	1.724 kg	
WBTCTSPRT24	1.996 kg	CE, nVent CADDY Wire Basket Tray System
WBTCTSPRT24BA	1.996 kg	CE, nVent CADDY Wire Basket Tray System
WBTCTSPRT24WH	1.996 kg	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

