

Modular Single Door, MCS



The mild steel single door combinable floor standing enclosure range, MCS, with a IP 55 protection degree, is available off the shelf in many different sizes. This enclosure range is well suited for many different applications. The risk for component failure, and with that unnecessary downtime, is eliminated as water and dust are prevented from entering the enclosure.

INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E61997

cUL Listed per CSA C22.2 No.0, No.0.4, No.14, No.94; Type 12; File No. E61997

NEMA/EEMAC Type 12

CSA, File No. 1442951: Type 12

IEC 62208 IP55

CE, UK CA, UL, DNV

FEATURES

Material: Frame: 1.5 mm painted steel. Door: 2 mm painted steel. Rear, roof and side panels: 1.5 mm painted steel. Mounting plate: 3 mm galvanized steel. Bottom plates: 1 mm galvanized steel.

Frame: Seam welded reversed open profiles with 25 mm hole pattern, according to DIN 43660. Including integrated external hole pattern.

Door: Mounted with four hinges allowing left or right hand opening. Including door frame with 25 mm hole pattern.

Rear panel: Fitted by M6 torx screws. Standard facilities for rear door mounting. RD version comes with rear door instead of rear panel.

Side panels: Supplied as an accessory.

Roof panel: Removable.

Lock: Espagnolette 4-point locking system. Does not interfere with the enclosure inner space. Standard double-bit lock with 3 mm insert. Standard inserts, cylinders, lift handles and T-handles are available as accessories.

Bottom plates: Consists of three or four (D>600) pieces.

Mounting plate: Double folded and slides into position. Adjustable in depth by steps of 25 mm, with the MPD02 accessory. Supplied, attached on the outside of the enclosure packaging.

Earthing: All panels are earthed through their fittings and are equipped with a separate earthing stud.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55 | TYPE 12 | IK 10.

Mounting requirements: Standard delivery ready for combined installation. For stand-alone installation add side panels.

Delivery: Frame with fitted door, rear panel, roof panel, bottom plates, mounting plate (not included for PER5 version) and door frame. For 400 mm wide enclosures, a mounting plate, bottom plates and door frame are not included. For enclosures 2200 mm height, delivery includes two CMB profiles mounted in depth. Delivery also includes earthing bolts. Delivered on a pallet which is identical to the width of the enclosure to allow baying without removal. All packing material is recyclable.

Material: Mild Steel
Finish: Powder Coated
Color: Light Gray
Color Code: RAL 7035
Body Thickness: 1.5mm
Door Thickness: 2mm

SPECIFICATIONS

Table 1/6

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Rear Door Included
MCS18064R5	MCS18064R5	1800mm	600mm	400mm	Yes	No
MCS18064R5-01		1800mm	600mm	400mm	No	No
MCS18064R5-02		1800mm	600mm	400mm	Yes	Yes
MCS18064R5-03		1800mm	600mm	400mm	No	Yes
MCS18064R5-04		1800mm	600mm	400mm	Yes	Yes
MCS18065R5	MCS18065R5	1800mm	600mm	500mm	Yes	No
MCS18065R5-01		1800mm	600mm	500mm	No	No
MCS18065R5-02		1800mm	600mm	500mm	Yes	Yes
MCS18065R5-03		1800mm	600mm	500mm	No	Yes
MCS18065R5-04		1800mm	600mm	500mm	Yes	Yes
MCS18066R5	MCS18066R5	1800mm	600mm	600mm	Yes	No
MCS18084R5	MCS18084R5	1800mm	800mm	400mm	Yes	No
MCS18084R5-01		1800mm	800mm	400mm	No	No
MCS18084R5-02		1800mm	800mm	400mm	Yes	Yes
MCS18084R5-03		1800mm	800mm	400mm	No	Yes
MCS18084R5-04		1800mm	800mm	400mm	Yes	Yes
MCS18085R5	MCS18085R5	1800mm	800mm	500mm	Yes	No
MCS18085R5-01		1800mm	800mm	500mm	No	No
MCS18085R5-02		1800mm	800mm	500mm	Yes	Yes
MCS18085R5-03		1800mm	800mm	500mm	No	Yes

Table 2/6

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Rear Door Included
MCS18085R5-04		1800mm	800mm	500mm	Yes	Yes
MCS18086R5	MCS18086R5	1800mm	800mm	600mm	Yes	No

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Rear Door Included
MCS18086R5-01		1800mm	800mm	600mm	No	No
MCS18086R5-02		1800mm	800mm	600mm	Yes	Yes
MCS18086R5-03		1800mm	800mm	600mm	No	Yes
MCS18086R5-04		1800mm	800mm	600mm	Yes	Yes
MCS18088R5	MCS18088R5	1800mm	800mm	800mm	Yes	No
MCS18088R5-01		1800mm	800mm	800mm	No	No
MCS18088R5-02		1800mm	800mm	800mm	Yes	Yes
MCS18088R5-03		1800mm	800mm	800mm	No	Yes
MCS18088R5-04		1800mm	800mm	800mm	Yes	Yes
MCS18104R5	MCS18104R5	1800mm	1000mm	400mm	Yes	No
MCS18104R5-01		1800mm	1000mm	400mm	No	No
MCS18104R5-02		1800mm	1000mm	400mm	Yes	Yes
MCS18104R5-03		1800mm	1000mm	400mm	No	Yes
MCS18104R5-04		1800mm	1000mm	400mm	Yes	Yes
MCS18105R5	MCS18105R5	1800mm	1000mm	500mm	Yes	No
MCS18105R5-01		1800mm	1000mm	500mm	No	No
MCS18105R5-02		1800mm	1000mm	500mm	Yes	Yes
MCS18105R5-03		1800mm	1000mm	500mm	No	Yes

Table 3/6

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Rear Door Included
MCS18105R5-04		1800mm	1000mm	500mm	Yes	Yes
MCS20064R5	MCS20064R5	2000mm	600mm	400mm	Yes	No
MCS20064R5-01		2000mm	600mm	400mm	No	No
MCS20064R5-02		2000mm	600mm	400mm	Yes	Yes
MCS20064R5-03		2000mm	600mm	400mm	No	Yes
MCS20064R5-04		2000mm	600mm	400mm	Yes	Yes
MCS20065R5	MCS20065R5	2000mm	600mm	500mm	Yes	No
MCS20065R5-01		2000mm	600mm	500mm	No	No
MCS20065R5-03		2000mm	600mm	500mm	No	Yes
MCS20065R5-04		2000mm	600mm	500mm	Yes	Yes
MCS20066R5	MCS20066R5	2000mm	600mm	600mm	Yes	No
MCS20066R5-01		2000mm	600mm	600mm	No	No
MCS20066R5-02		2000mm	600mm	600mm	Yes	Yes
MCS20066R5-03		2000mm	600mm	600mm	No	Yes
MCS20066R5-04		2000mm	600mm	600mm	Yes	Yes
MCS20068R5	MCS20068R5	2000mm	600mm	800mm	Yes	No

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Rear Door Included
MCS20068R5-01		2000mm	600mm	800mm	No	No
MCS20068R5-02		2000mm	600mm	800mm	Yes	Yes
MCS20068R5-03		2000mm	600mm	800mm	No	Yes
MCS20068R5-04		2000mm	600mm	800mm	Yes	Yes

Table 4/6

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Rear Door Included
MCS20084R5	MCS20084R5	2000mm	800mm	400mm	Yes	No
MCS20084R5-01		2000mm	800mm	400mm	No	No
MCS20084R5-02		2000mm	800mm	400mm	Yes	Yes
MCS20084R5-03		2000mm	800mm	400mm	No	Yes
MCS20084R5-04		2000mm	800mm	400mm	Yes	Yes
MCS20085R5	MCS20085R5	2000mm	800mm	500mm	Yes	No
MCS20085R5-01		2000mm	800mm	500mm	No	No
MCS20085R5-02		2000mm	800mm	500mm	Yes	Yes
MCS20085R5-03		2000mm	800mm	500mm	No	Yes
MCS20085R5-04		2000mm	800mm	500mm	Yes	Yes
MCS20086R5	MCS20086R5	2000mm	800mm	600mm	Yes	No
MCS20086R5-01		2000mm	800mm	600mm	No	No
MCS20086R5-02		2000mm	800mm	600mm	Yes	Yes
MCS20086R5-03		2000mm	800mm	600mm	No	Yes
MCS20086R5-04		2000mm	800mm	600mm	Yes	Yes
MCS20088R5	MCS20088R5	2000mm	800mm	800mm	Yes	No
MCS20088R5-01		2000mm	800mm	800mm	No	No
MCS20088R5-02		2000mm	800mm	800mm	Yes	Yes
MCS20088R5-03		2000mm	800mm	800mm	No	Yes
MCS20088R5-04		2000mm	800mm	800mm	Yes	Yes

Table 5/6

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Rear Door Included
MCS20105R5	MCS20105R5	2000mm	1000mm	500mm	Yes	No
MCS20105R5-01		2000mm	1000mm	500mm	No	No
MCS20105R5-02		2000mm	1000mm	500mm	Yes	Yes
MCS20105R5-03		2000mm	1000mm	500mm	No	Yes
MCS20105R5-04		2000mm	1000mm	500mm	Yes	Yes
MCS20106R5	MCS20106R5	2000mm	1000mm	600mm	Yes	No
MCS20106R5-01		2000mm	1000mm	600mm	No	No


Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Rear Door Included
MCS20106R5-02		2000mm	1000mm	600mm	Yes	Yes
MCS20106R5-03		2000mm	1000mm	600mm	No	Yes
MCS20106R5-04		2000mm	1000mm	600mm	Yes	Yes
MCS20108R5	MCS20108R5	2000mm	1000mm	800mm	Yes	No
MCS20108R5-01		2000mm	1000mm	800mm	No	No
MCS20108R5-02		2000mm	1000mm	800mm	Yes	Yes
MCS20108R5-03		2000mm	1000mm	800mm	No	Yes
MCS20108R5-04		2000mm	1000mm	800mm	Yes	Yes
MCS22066R5	MCS22066R5	2200mm	600mm	600mm	Yes	No
MCS22066R5-01		2200mm	600mm	600mm	No	No
MCS22066R5-02		2200mm	600mm	600mm	Yes	Yes
MCS22066R5-03		2200mm	600mm	600mm	No	Yes
MCS22066R5-04		2200mm	600mm	600mm	Yes	Yes

Table 6/6

Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included	Rear Door Included
MCS22086R5	MCS22086R5	2200mm	800mm	600mm	Yes	No
MCS22086R5-01		2200mm	800mm	600mm	No	No
MCS22086R5-02		2200mm	800mm	600mm	Yes	Yes
MCS22086R5-03		2200mm	800mm	600mm	No	Yes
MCS22086R5-04		2200mm	800mm	600mm	Yes	Yes
MCS22088R5	MCS22088R5	2200mm	800mm	800mm	Yes	No
MCS22088R5-01		2200mm	800mm	800mm	No	No
MCS22088R5-02		2200mm	800mm	800mm	Yes	Yes
MCS22088R5-03		2200mm	800mm	800mm	No	Yes
MCS22088R5-04		2200mm	800mm	800mm	Yes	Yes
MCS20065R5-02		2000mm	600mm	500mm	Yes	Yes
MCS18066R501		1800mm	600mm	600mm	No	No
MCS18066R502		1800mm	600mm	600mm	Yes	Yes
MCS18066R503		1800mm	600mm	600mm	No	No
MCS18066R504		1800mm	600mm	600mm	Yes	Yes

ADDITIONAL PRODUCT DETAILS

SPM mild steel side panels must be ordered separately to close the cabinets (individual or assembled), in order to maintain the protection rating.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.