


# Wire Basket Tray PreForm Intersection



The nVent CADDY Wire Basket Tray PreForm Intersection is a precision-engineered solution designed to streamline cable tray installations at multi-pathway junctions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Intersection delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Intersection significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## FEATURES

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Material:** Steel  
**Finish:** Pregalvanized;Polyurethane



## SPECIFICATIONS

Table 1/2


| Catalog Number | Color | Height (H) | Width (W) | Length (L) | Hole Size (HS) | Radius (R) |
|----------------|-------|------------|-----------|------------|----------------|------------|
| WBTI2X12       |       | 50.8 mm    | 711.2 mm  | 711.2mm    | 19.05 mm       | 94.64mm    |
| WBTI2X12BA     | Black | 50.8 mm    | 711.2 mm  | 711.2mm    | 19.05 mm       | 94.64mm    |
| WBTI2X18       |       | 50.8 mm    | 861.06 mm | 861.06mm   | 19.05 mm       | 94.64mm    |
| WBTI2X18BA     | Black | 50.8 mm    | 861.06 mm | 861.06mm   | 19.05 mm       | 94.64mm    |
| WBTI2X24       |       | 50.8 mm    | 1016 mm   | 1016mm     | 19.05 mm       | 94.64mm    |
| WBTI2X24BA     | Black | 50.8 mm    | 1016 mm   | 1016mm     | 19.05 mm       | 94.64mm    |
| WBTI2X4        |       | 50.8 mm    | 511.48 mm | 511.48mm   |                | 94.64mm    |
| WBTI2X4BA      | Black | 50.8 mm    | 511.48 mm | 511.48mm   |                | 94.64mm    |
| WBTI2X6        |       | 50.8 mm    | 561.34 mm | 561.34mm   |                | 94.64mm    |

| Catalog Number | Color | Height (H) | Width (W) | Length (L) | Hole Size (HS) | Radius (R) |
|----------------|-------|------------|-----------|------------|----------------|------------|
| WBTI2X6BA      | Black | 50.8 mm    | 561.34 mm | 561.34mm   |                | 94.64mm    |
| WBTI2X8        |       | 50.8 mm    | 612.14 mm | 612.14mm   |                | 94.64mm    |
| WBTI2X8BA      | Black | 50.8 mm    | 612.14 mm | 612.14mm   |                | 94.64mm    |

Table 2/2

| Catalog Number | Unit Weight | Certifications                                   |
|----------------|-------------|--------------------------------------------------|
| WBTI2X12       | 3.175 kg    | UL, CE, nVent CADDY Wire Basket Tray System, cUL |
| WBTI2X12BA     | 3.175 kg    | CE, nVent CADDY Wire Basket Tray System          |
| WBTI2X18       | 5.443 kg    | CE, nVent CADDY Wire Basket Tray System, UL, cUL |
| WBTI2X18BA     | 5.443 kg    | CE, nVent CADDY Wire Basket Tray System          |
| WBTI2X24       | 8.165 kg    | UL, CE, nVent CADDY Wire Basket Tray System, cUL |
| WBTI2X24BA     | 8.165 kg    | CE, nVent CADDY Wire Basket Tray System          |
| WBTI2X4        | 0.907 kg    | CE, nVent CADDY Wire Basket Tray System, UL, cUL |
| WBTI2X4BA      | 0.907 kg    | CE, nVent CADDY Wire Basket Tray System          |
| WBTI2X6        | 1.361 kg    | cUL, CE, nVent CADDY Wire Basket Tray System, UL |
| WBTI2X6BA      | 1.361 kg    | CE, nVent CADDY Wire Basket Tray System          |
| WBTI2X8        | 2.268 kg    | UL, cUL, CE, nVent CADDY Wire Basket Tray System |
| WBTI2X8BA      | 2.268 kg    | CE, nVent CADDY Wire Basket Tray System          |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

