


Grounding Busbar



Proper bonding is essential to create an equipotential plane between service grounds and equipment during fault and transient conditions. This equipotential plane provides a near-zero voltage differential, and serves to protect people and equipment during these events. The grounding busbar is the most popular bonding product in use today.

FEATURES

Provides a convenient, single-point grounding and bonding location


Conductors are welded to the bar using a nVent ERICO Cadweld exothermic connection or are mechanically fastened by using lugs

Custom bars can be designed and manufactured to customer specifications

Material: Copper



DIAGRAMS





SPECIFICATIONS

Table 1/2

Catalog Number	Busbar Configuration	Hole Pattern	Mounting Hole Size	Length	Width	Thickness
EGBA14206EET	Busbar, Insulators and Brackets	EE	11.1mm	152mm	51 mm	6.4 mm
EGBA14212BBT	Busbar, Insulators and Brackets	BB	11.1mm	305mm	51 mm	6.4 mm
EGBA14212EET	Busbar, Insulators and Brackets	EE	11.1mm	305mm	51 mm	6.4 mm
EGBA14212HH	Busbar, Insulators and Brackets	HH	11.1mm	305mm	51 mm	6.4 mm
EGBA14212TES	Busbar, Insulators and Brackets	TES	11.1mm	305mm	51 mm	6.4 mm
EGBA14215EET	Busbar, Insulators and Brackets	EE	11.1mm	381mm	51 mm	6.4 mm
EGBA14215TES	Busbar, Insulators and Brackets	TES	11.1mm	381mm	51 mm	6.4 mm
EGBA14216HH	Busbar, Insulators and Brackets	HH	11.1mm	406mm	51 mm	6.4 mm
EGBA14220DGT	Busbar, Insulators and Brackets	DG	11.1mm	508mm	51 mm	6.4 mm
EGBA14224EET	Busbar, Insulators and Brackets	EE	11.1mm	610mm	51 mm	6.4 mm
EGBA14224GGT	Busbar, Insulators and Brackets	GG	11.1mm	610mm	51 mm	6.4 mm
EGBA14240EET	Busbar, Insulators and Brackets	EE	11.1mm	1016mm	51 mm	6.4 mm
EGBA14412CC	Busbar, Insulators and Brackets	CC	11.1mm	305mm	102 mm	6.4 mm
EGBA14420HIG	Busbar, Insulators and Brackets	HIG	11.1mm	508mm	102 mm	6.4 mm
EGBA14420LL	Busbar, Insulators and Brackets	LL	11.1mm	508mm	102 mm	6.4 mm
EGBA14424DDT	Busbar, Insulators and Brackets	DD	11.1mm	610mm	102 mm	6.4 mm
EGBA14424MM	Busbar, Insulators and Brackets	MM	11.1mm	610mm	102 mm	6.4 mm
EGBA14436CC	Busbar, Insulators and Brackets	CC	11.1mm	914mm	102 mm	6.4 mm
EGBA14612AA	Busbar, Insulators and Brackets	AA	11.1mm	305mm	152 mm	6.4 mm
EGBA14618AA	Busbar, Insulators and Brackets	AA	11.1mm	457mm	152 mm	6.4 mm

Table 2/2

Catalog Number	Busbar Configuration	Hole Pattern	Mounting Hole Size	Length	Width	Thickness
EGBB14212JJ	Busbar and Brackets	JJ	11.1mm	305mm	51 mm	6.4 mm
EGBC14212NN	Busbar Only	NN	11.1mm	305mm	51 mm	6.4 mm
EGBC14412LLT	Busbar Only	LL	11.1mm	305mm	102 mm	6.4 mm
EGBD14224BB	Busbar and Insulators	BB	11.1mm	610mm	51 mm	6.4 mm

Table 1/2

Catalog Number	Tin Plating	Pigtail Included
EGBA14206EET	Yes	No
EGBA14212BBT	Yes	No
EGBA14212EET	Yes	No
EGBA14212HH	No	No
EGBA14212TES	No	No
EGBA14215EET	Yes	No
EGBA14215TES	No	No
EGBA14216HH	No	No
EGBA14220DGT	Yes	No
EGBA14224EET	Yes	No
EGBA14224GGT	Yes	No
EGBA14240EET	Yes	No
EGBA14412CC	No	No
EGBA14420HIG	No	No
EGBA14420LL	No	No
EGBA14424DDT	Yes	No
EGBA14424MM	No	No
EGBA14436CC	No	No
EGBA14612AA	No	No
EGBA14618AA	No	No

Table 2/2

Catalog Number	Tin Plating	Pigtail Included
EGBB14212JJ	No	No
EGBC14212NN	No	No
EGBC14412LLT	Yes	No
EGBD14224BB	No	No

ADDITIONAL PRODUCT DETAILS

Diagrams are representative of the hole pattern. The number of holes is dependent on the length of the grounding busbar.

Additional configurations are available by special order. Note special orders may incur additional lead time.

EGB-A-14-4-12-CC-T-1T-K		
EGB	ERICO Grounding Busbar Designation	
A	Configuration	A: Busbar, Insulators and Brackets B: Busbar and Brackets C: Busbar Only D: Busbar and Insulators
14	Thickness (")	14: 1/4" · 38: 3/8" · 12: 1/2"
4	Width (")	
12	Length (")	Rounded to the nearest inch, 144" max
CC	Hole Pattern	Diagrams are representative of the hole pattern. The number of holes is dependent on the length of the grounding busbar.
T*	Tin Plating	
1T*	ERICO Cable Code	1K: #4 Sol Tin · 1T: #2 Sol Tin 2C: 1/0 · 2G: 2/0 · 2L: 3/0 · 2Q: 4/0 2V: 250 kcmil · 3D: 350 kcmil · 3Q: 500 kcmil · 4L: 750 kcmil
K*	Pigtail Length (')	A:1 · B:2 · C:3 · D:4 · E:5 · F:6 · G:7 · H:8 · J:9 · K:10 · L:12 · M:14 · N:16 P:18 · Q:20 · R:22 · S:24 · T:26 · U:28 · V:30 · W:32 · X:34 · Y:36 · Z:38

* Empty if none

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.