



34560-142

FEATURES

< 28 HP not to print

Combinations of horizontal rails and side panels

		ΔT_{max} can be combined ΔT_{max} combination not recommended			
 Double glazing	 Single glazing	+	+	+	+
	 Double glazing	+	reduced Uf possible (see calculation)	reduced Uf possible (see calculation)	+
 Double glazing	 Single glazing	+	+	+	+
	 Double glazing	+	reduced Uf possible (see calculation)	reduced Uf possible (see calculation)	+
 Double glazing	 Single glazing	+	+	+	+
	 Double glazing	+	reduced Uf possible (see calculation)	reduced Uf possible (see calculation)	+

PRODUCT ATTRIBUTES

Gross Weight: 0.067kg



ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

