

Cable Clamp



FEATURES

For installation of single or multiple cables directly against concrete surface

Discrete low-profile clamp reduces visual impact

Halogen free


UV-stabilized

Material: Polypropylene

Temperature: -10 to 85 °C

SPECIFICATIONS

Catalog Number	Article Number	Diameter (Ø)	Drill Hole Diameter	Drill Hole Depth	Static Load
SCDKS2040	800053	20 - 40 mm	6mm	30mm	170N
SCDKS313	800050	3 - 13 mm	6mm	30mm	170N
SCDKS620	800051	6 - 20 mm	6mm	30mm	170N
SCDKS828	800052	8 - 28 mm	6mm	30mm	170N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

