

Cable to Flange Clip



FEATURES


Provides support for low voltage cables

Requires only a hammer to install

Material: Spring Steel
Finish: nVent CADDY Armour

SPECIFICATIONS

Catalog Number	Article Number	Flange Thickness (FT)	Outer Diameter (OD)	A
2H41012A	170460	2 - 3 mm	10.9 - 13 mm	25 mm
2H41214A	170470	2 - 3 mm	12.4 - 16 mm	25 mm
4H241012A	170480	3 - 8 mm	10.9 - 13 mm	25 mm
4H241214A	170630	3 - 8 mm	12.4 - 16 mm	25 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

