


Cantilever Arm with EOL Channel

FEATURES

Perforated, cold rolled

Slotted backplate



Material: Steel
Finish: Electrogalvanized




SPECIFICATIONS

Catalog Number	Article Number	Length (L)
CEOL13H0180EG	599879	180mm
CEOL13H0300EG	599880	300mm

Height (H): 120 mm
Width (W): 40 mm
Thickness (T): 1.25 mm
A: 18 mm
B: 27 mm
C: 15.5 mm
D: 60 mm
E: 4 mm
X: 11 x 18 mm
Y: 8.5 x 20 mm
Hole Size (HS): 10.5 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

