

Twist-In Insert for Perforated Cable Tray

CATALOG NUMBER

SCEDV


FEATURES

For installation of plastic conduit clamps and clips on cable trays with slots

Passed 650°C glowing/hot-wire test per EN 60695-2

Halogen free

UV-stabilized



PRODUCT ATTRIBUTES

Article Number: 800035

Material: Nylon

Temperature: -20 to 85 °C

A: 20 mm


B: 11 mm

C: 16 mm

D: 6 mm

E: 6 - 9 mm

Thickness (T): 0.50 - 1.1 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

