

Telescoping box bracket, 280–458 mm stud space, 38 mm, 54 mm box depth

CATALOG NUMBER

TSGB16



The nVent CADDY Telescoping Screw Gun Box Bracket is a simple and intuitive support for mounting electrical boxes within stud wall applications. This solution delivers traditional mounting, which allows the bracket to bend for multiple depths and install easily with single or multiple electrical boxes. The notched and clearly marked bend points make installation safe, fast and easy.

FEATURES

- Designed for both single and multiple box mounting
- Unique single-component break-apart design
- Stamped inch markings and pilot holes accelerate precise box conduit mounting
- Pilot holes allow for easy access with a screwdriver
- Adjustable for non-standard stud spacing
- Interlocking tab prevents accidental disassembly



PRODUCT ATTRIBUTES

- Article Number: 187190
- Material: Steel
- Finish: Pregalvanized
- Stud Spacing: 280 - 458 mm
- Box Depth: 38mm;54mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

