

# Heavy Duty Pipe Clamp per DIN 3567



## FEATURES

For high static requirements in industrial construction

Suitable for fix point applications

Can be welded onto T-beam to form a sliding element

**Material:** Steel

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Finish             | Outer Diameter (OD) | NB/DN | Hole Size (HS) | Width (W) |
|----------------|----------------|--------------------|---------------------|-------|----------------|-----------|
| DIN021HD       | 400197         | Hot-Dip Galvanized | 21.3 mm             | 15    | 11.5 mm        | 30 mm     |
| DIN021PL       | 400149         | Plain              | 21.3 mm             | 15    | 11.5 mm        | 30 mm     |
| DIN027HD       | 400199         | Hot-Dip Galvanized | 26.9 mm             | 20    | 11.5 mm        | 30 mm     |
| DIN027PL       | 400151         | Plain              | 26.9 mm             | 20    | 11.5 mm        | 30 mm     |
| DIN034HD       | 400201         | Hot-Dip Galvanized | 33.7 mm             | 25    | 11.5 mm        | 30 mm     |
| DIN034PL       | 400153         | Plain              | 33.7 mm             | 25    | 11.5 mm        | 30 mm     |
| DIN042HD       | 400203         | Hot-Dip Galvanized | 42.4 mm             | 32    | 11.5 mm        | 30 mm     |
| DIN042PL       | 400155         | Plain              | 42.4 mm             | 32    | 11.5 mm        | 30 mm     |
| DIN048HD       | 400205         | Hot-Dip Galvanized | 48.3 mm             | 40    | 11.5 mm        | 30 mm     |
| DIN048PL       | 400157         | Plain              | 48.3 mm             | 40    | 11.5 mm        | 30 mm     |
| DIN060HD       | 400208         | Hot-Dip Galvanized | 60.3 mm             | 50    | 14 mm          | 40 mm     |
| DIN060PL       | 400160         | Plain              | 60.3 mm             | 50    | 14 mm          | 40 mm     |

| Catalog Number | Article Number | Finish             | Outer Diameter (OD) | NB/DN | Hole Size (HS) | Width (W) |
|----------------|----------------|--------------------|---------------------|-------|----------------|-----------|
| DIN076HD       | 400210         | Hot-Dip Galvanized | 76.1 mm             | 65    | 14 mm          | 40 mm     |
| DIN076PL       | 400162         | Plain              | 76.1 mm             | 65    | 14 mm          | 40 mm     |
| DIN089HD       | 400212         | Hot-Dip Galvanized | 88.9 mm             | 80    | 14 mm          | 40 mm     |
| DIN089PL       | 400164         | Plain              | 88.9 mm             | 80    | 14 mm          | 40 mm     |
| DIN102HD       | 400214         | Hot-Dip Galvanized | 102 mm              | 90    | 18 mm          | 50 mm     |
| DIN102PL       | 400166         | Plain              | 102 mm              | 90    | 18 mm          | 50 mm     |
| DIN114HD       | 400216         | Hot-Dip Galvanized | 114.3 mm            | 100   | 18 mm          | 50 mm     |
| DIN114PL       | 400168         | Plain              | 114.3 mm            | 100   | 18 mm          | 50 mm     |

Table 2/2

| Catalog Number | Article Number | Finish             | Outer Diameter (OD) | NB/DN | Hole Size (HS) | Width (W) |
|----------------|----------------|--------------------|---------------------|-------|----------------|-----------|
| DIN140HD       | 400219         | Hot-Dip Galvanized | 139.7 mm            | 125   | 18 mm          | 50 mm     |
| DIN140PL       | 400171         | Plain              | 139.7 mm            | 125   | 18 mm          | 50 mm     |
| DIN168HD       | 400222         | Hot-Dip Galvanized | 168.3 mm            | 150   | 18 mm          | 50 mm     |
| DIN168PL       | 400174         | Plain              | 168.3 mm            | 150   | 18 mm          | 50 mm     |
| DIN219HD       | 400225         | Hot-Dip Galvanized | 219.1 mm            | 200   | 18 mm          | 50 mm     |
| DIN219PL       | 400177         | Plain              | 219.1 mm            | 200   | 18 mm          | 50 mm     |
| DIN273HD       | 400229         | Hot-Dip Galvanized | 273 mm              | 250   | 23 mm          | 60 mm     |
| DIN273PL       | 400181         | Plain              | 273 mm              | 250   | 23 mm          | 60 mm     |
| DIN323HD       | 400233         | Hot-Dip Galvanized | 323.9 mm            | 300   | 23 mm          | 60 mm     |
| DIN323PL       | 400185         | Plain              | 323.9 mm            | 300   | 23 mm          | 60 mm     |
| DIN355HD       | 400234         | Hot-Dip Galvanized | 355.6 mm            | 350   | 23 mm          | 60 mm     |
| DIN355PL       | 400186         | Plain              | 355.6 mm            | 350   | 23 mm          | 60 mm     |
| DIN406HD       | 400236         | Hot-Dip Galvanized | 406.4 mm            | 400   | 27 mm          | 70 mm     |
| DIN406PL       | 400188         | Plain              | 406.4 mm            | 400   | 27 mm          | 70 mm     |
| DIN457HD       | 400238         | Hot-Dip Galvanized | 457 mm              | 450   | 27 mm          | 70 mm     |
| DIN457PL       | 400190         | Plain              | 457 mm              | 450   | 27 mm          | 70 mm     |
| DIN508HD       | 400239         | Hot-Dip Galvanized | 508 mm              | 500   | 27 mm          | 70 mm     |
| DIN508PL       | 400191         | Plain              | 508 mm              | 500   | 27 mm          | 70 mm     |
| DIN610HD       | 400241         | Hot-Dip Galvanized | 610 mm              | 600   | 27 mm          | 70 mm     |
| DIN610PL       | 400193         | Plain              | 610 mm              | 600   | 27 mm          | 70 mm     |

Table 1/2

| Catalog Number | Article Number | Thickness (T) | A     |
|----------------|----------------|---------------|-------|
| DIN021HD       | 400197         | 5 mm          | 58 mm |
| DIN021PL       | 400149         | 5 mm          | 58 mm |


| Catalog Number | Article Number | Thickness (T) | A      |
|----------------|----------------|---------------|--------|
| DIN027HD       | 400199         | 5 mm          | 64 mm  |
| DIN027PL       | 400151         | 5 mm          | 64 mm  |
| DIN034HD       | 400201         | 5 mm          | 72 mm  |
| DIN034PL       | 400153         | 5 mm          | 72 mm  |
| DIN042HD       | 400203         | 5 mm          | 82 mm  |
| DIN042PL       | 400155         | 5 mm          | 82 mm  |
| DIN048HD       | 400205         | 5 mm          | 88 mm  |
| DIN048PL       | 400157         | 5 mm          | 88 mm  |
| DIN060HD       | 400208         | 6 mm          | 108 mm |
| DIN060PL       | 400160         | 6 mm          | 108 mm |
| DIN076HD       | 400210         | 6 mm          | 122 mm |
| DIN076PL       | 400162         | 6 mm          | 122 mm |
| DIN089HD       | 400212         | 6 mm          | 136 mm |
| DIN089PL       | 400164         | 6 mm          | 136 mm |
| DIN102HD       | 400214         | 8 mm          | 166 mm |
| DIN102PL       | 400166         | 8 mm          | 166 mm |
| DIN114HD       | 400216         | 8 mm          | 178 mm |
| DIN114PL       | 400168         | 8 mm          | 178 mm |

Table 2/2

| Catalog Number | Article Number | Thickness (T) | A      |
|----------------|----------------|---------------|--------|
| DIN140HD       | 400219         | 8 mm          | 204 mm |
| DIN140PL       | 400171         | 8 mm          | 204 mm |
| DIN168HD       | 400222         | 8 mm          | 232 mm |
| DIN168PL       | 400174         | 8 mm          | 232 mm |
| DIN219HD       | 400225         | 8 mm          | 284 mm |
| DIN219PL       | 400177         | 8 mm          | 284 mm |
| DIN273HD       | 400229         | 8 mm          | 348 mm |
| DIN273PL       | 400181         | 8 mm          | 348 mm |
| DIN323HD       | 400233         | 8 mm          | 398 mm |
| DIN323PL       | 400185         | 8 mm          | 398 mm |
| DIN355HD       | 400234         | 8 mm          | 432 mm |
| DIN355PL       | 400186         | 8 mm          | 432 mm |
| DIN406HD       | 400236         | 10 mm         | 498 mm |
| DIN406PL       | 400188         | 10 mm         | 498 mm |
| DIN457HD       | 400238         | 10 mm         | 548 mm |

| Catalog Number | Article Number | Thickness (T) | A      |
|----------------|----------------|---------------|--------|
| DIN457PL       | 400190         | 10 mm         | 548 mm |
| DIN508HD       | 400239         | 10 mm         | 600 mm |
| DIN508PL       | 400191         | 10 mm         | 600 mm |
| DIN610HD       | 400241         | 10 mm         | 710 mm |
| DIN610PL       | 400193         | 10 mm         | 710 mm |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

