


Speedway Cable Ladder Flat Elbow, 45°



FEATURES

Creates a 45° corner change in cable tray direction

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant


Responsive design and layout services, including seismic

Material: Steel
Finish: Hot-Dip Galvanized



SPECIFICATIONS

Catalog Number	Article Number	Width (W)	Angle (a)	A	B	C	D
CL110X150FE45HD	840100	150 mm	45 °	326 mm	460 mm	80 mm	110 mm
CL110X300FE45HD	840110	300 mm	45 °	476 mm	566 mm	80 mm	110 mm
CL110X450FE45HD	840120	450 mm	45 °	626 mm	673 mm	80 mm	110 mm
CL110X600FE45HD	840130	600 mm	45 °	776 mm	779 mm	80 mm	110 mm
CL110X750FE45HD	840140	750 mm	45 °	926 mm	885 mm	80 mm	110 mm
CL110X900FE45HD	840150	900 mm	45 °	1076 mm	991 mm	80 mm	110 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

