

# nVent CADDY Pyramid Universal Support



## FEATURES

Captive stainless steel nuts allow for custom attachment methods to the support base including easy attachment of stainless steel strut, threaded rod or other project-specific hardware

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Includes square holes for creating an H-Frame with a 12" (305 mm) cross support (PBU16 only)

Base is manufactured from UV-stabilized thermoplastic material

**Material:** Polyethylene;Polypropylene;Stainless Steel 18-8 (EN 1.4305)  
**Temperature:** -45 to 65 °C  
**Static Load Safety Factor:** 3:1

## SPECIFICATIONS




Table 1/2

| Catalog Number | Article Number | Length 1 (L1) | Length 2 (L2) | Height (H) | Width (W) | Thread Size (TS) |
|----------------|----------------|---------------|---------------|------------|-----------|------------------|
| PBU10          | 360489         | 254 mm        | 317.5 mm      | 101.6 mm   | 203 mm    | 3/8" UNC         |
| PBU16          | 360490         | 406 mm        | 483 mm        | 101.6 mm   | 203 mm    | 3/8" UNC         |

| Catalog Number | Article Number | Length 1 (L1) | Length 2 (L2) | Height (H) | Width (W) | Thread Size (TS) |
|----------------|----------------|---------------|---------------|------------|-----------|------------------|
| PBU6           | 360488         | 139.7 mm      | 203 mm        | 101.6 mm   | 152 mm    | 3/8" UNC         |

| Table 2/2      |                |               |          |         |                      |             |
|----------------|----------------|---------------|----------|---------|----------------------|-------------|
| Catalog Number | Article Number | Hole Quantity | A        | B       | Surface Area         | Static Load |
| PBU10          | 360489         | 2             | 218.4 mm |         | 59355mm <sup>2</sup> | 4450N       |
| PBU16          | 360490         | 2             | 165.1 mm |         | 91613mm <sup>2</sup> | 6670N       |
| PBU6           | 360488         | 3             | 114.3 mm | 57.2 mm | 26452mm <sup>2</sup> | 1330N       |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

