

# Side Plinths Mild Steel, PS



The extra space created by the plinth is closed off by using these panels in order to restrict access to this area.

## FEATURES

Description: Side panels to cover the openings in the sides of the PF/PV plinths. Double folded panels for maximum strength. Compatible with combinable and semi-compact enclosure ranges.

Material: 1.5 mm steel plate.

Finish: RAL 7022 structured powder coating.

Pack quantity: 2 panels. Mounting accessories included with PF/PV.

**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color:** Umbra Gray  
**Color Code:** RAL 7022  
**Thickness:** 1.5mm

## SPECIFICATIONS

| Catalog Number | Article Number | Height | Width | Depth | Product Family | Enclosure Material |
|----------------|----------------|--------|-------|-------|----------------|--------------------|
| PS1050         | PS1050         | 100mm  | 500mm | 27mm  | Free-Standing  | Mild Steel         |
| PS2050         | PS2050         | 200mm  | 500mm | 27mm  | Free-Standing  | Mild Steel         |
| PS1040         | PS1040         | 100mm  | 400mm | 27mm  | Free-Standing  | Mild Steel         |
| PS2040         | PS2040         | 200mm  | 400mm | 27mm  | Free-Standing  | Mild Steel         |
| PS1060         | PS1060         | 100mm  | 600mm | 27mm  | Free-Standing  | Mild Steel         |
| PS2060         | PS2060         | 200mm  | 600mm | 27mm  | Free-Standing  | Mild Steel         |
| PS1080         | PS1080         | 100mm  | 800mm | 27mm  | Free-Standing  | Mild Steel         |
| PS2080         | PS2080         | 200mm  | 800mm | 27mm  | Free-Standing  | Mild Steel         |
| PS1030         | PS1030         | 100mm  | 300mm | 27mm  | Free-Standing  | Mild Steel         |
| PS2030         | PS2030         | 200mm  | 300mm | 27mm  | Free-Standing  | Mild Steel         |
| PS1100         | PS1100         | 100mm  | 999mm | 27mm  | Free-Standing  | Mild Steel         |
| PS2100         | PS2100         | 200mm  | 999mm | 27mm  | Free-Standing  | Mild Steel         |

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.