


3000 Beam Clamp Kit

FEATURES

Medium duty system

Includes clamp and U channel



Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Length (L)	Height (H)	Width (W)	Thickness (T)	Flange Thickness (FT)
3300EG	570410	300mm	15 mm	30 mm	2.5 mm	15 mm Max
3400EG	570420	400mm	15 mm	30 mm	2.5 mm	15 mm Max
3500EG	570430	500mm	15 mm	30 mm	2.5 mm	15 mm Max
3600EG	570440	600mm	15 mm	30 mm	2.5 mm	15 mm Max


Table 2/2

Catalog Number	Article Number	Hole Size (HS)	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)
3300EG	570410	13 mm	3700N	490N	390N
3400EG	570420	13 mm	3700N	490N	390N
3500EG	570430	13 mm	3700N	490N	390N
3600EG	570440	13 mm	3700N	490N	390N

A: 40 mm
B: 100 mm

C: 150 mm
D: 25 mm
E: 31.5 mm
X: 10.5 x 25 mm
Screw Diameter (Sc): 8
Torque (TQ): 30 N·m

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America	Europe	Europe	APAC
+1.800.753.9221	Netherlands:	Germany:	Shanghai:
Option 1 – Customer Care	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
Option 2 – Technical	France:	Other Countries:	Sydney:
Support	+33 800 901 793	+31 13 5835404	+61 2 9751 8500

