

Swivel Post Base Bracket for Strut Type A, EG



CATALOG NUMBER

SNAEG

FEATURES

Suitable for sloped walls and ceilings

Two bolts and nuts included

PRODUCT ATTRIBUTES

Article Number: 311905

Material: Steel

Finish: Electrogalvanized

Height (H): 150 mm

Length (L): 106mm

Thickness (T): 3 mm

Diameter (Ø): 11 mm

A: 42 mm

B: 11 mm

C: 20 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

