


# LHX+ Air/Liquid Heat Exchanger



RackChiller In-Row Coolers (IRC) are designed to deliver localized/supplemental energy efficient cooling in data centers. RackChiller IRC is a modular and scalable precision cooling solution that can replace or supplement traditional data center cooling infrastructure.

## FEATURES

19" mountable Air/liquid heat exchanger with fan

Easy replaceable fans without dismounting the heat exchanger

Coolant feed from top or bottom

**Airflow Direction:** Front to Top  
**Depth:** 500mm  
**Product Type:** Air/Liquid Heat Exchanger

## SPECIFICATIONS

Table 1/2

| Catalog Number | Fan Quantity | Input Voltage AC | Package Quantity | Supply Voltage | Redundant Power Supply | Coolant Feed |
|----------------|--------------|------------------|------------------|----------------|------------------------|--------------|
| 29714-016      | 2            | 100 – 240V       | 1                | 230V min       | No                     | Bottom       |
| 29714-017      | 1            | 100 – 240V       | 1                | 230V min       | No                     | Bottom       |

Table 2/2

| Catalog Number | Height | Material | Product Family | Width | Works With            |
|----------------|--------|----------|----------------|-------|-----------------------|
| 29714-016      | 266mm  | Aluminum | Cooling        | 426mm | Varistar, Varistar CP |
| 29714-017      | 266mm  | Aluminum | Cooling        | 426mm | Varistar, Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please order separately: Monitoring via Control unit, water control package, display and door contact switch.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

