

Cantilever Arm with E0 Channel, 660 mm

CATALOG NUMBER

CE015H0660EG

FEATURES

Perforated, cold rolled

Slotted backplate



PRODUCT ATTRIBUTES

Article Number: 599925

Material: Steel

Finish: Electrogalvanized

Length (L): 660mm

Height (H): 120 mm

Width (W): 40 mm

Thickness (T): 1.5 mm

A: 30 mm

B: 27 mm

C: 15.5 mm

D: 60 mm

E: 6 mm

X: 11 x 18 mm

Y: 8.5 x 20 mm

Hole Size (HS): 10.5 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

