

# HW Wedge Nut for Dovetail Deck, M6 Rod, 15°

## CATALOG NUMBER

**HW6**

## FEATURES

Trapeze nut for hanging threaded rod from steel ceilings

Installs easily

Fits several composite floor decking profiles



## PRODUCT ATTRIBUTES

Article Number: 187270

Material: Steel

Finish: Electrogalvanized

Rod Size (RS): 6

Angle (a): 15 °

A: 25 mm



B: 12 mm

C: 12 mm

Static Load: 1200N

| Metal Decking Compatibility for Wedge Nuts |               |     |     |     |      |      |       |       |
|--------------------------------------------|---------------|-----|-----|-----|------|------|-------|-------|
| Part Number                                |               | HW4 | HW6 | HW8 | HW10 | HW12 | PHWC6 | PHWC8 |
| TATA                                       | Comflor 51+   | X   | X   | X   | X    | X    |       |       |
|                                            | Comflor 60/75 |     |     |     |      |      | X     | X     |
|                                            | Comflor 80/95 |     |     |     |      |      | X     | X     |
|                                            | Ribdeck 80    |     |     |     |      |      | X     | X     |
| SMD                                        | R51+          | X   | X   | X   | X    | X    |       |       |
| KINGSPAN                                   | Multideck 50  | X   | X   | X   | X    | X    |       |       |
| CMF                                        | Metfloor 55   | X   | X   | X   | X    | X    |       |       |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

