

Wire Basket Tray L Bracket



The nVent CADDY Wire Basket Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multi-tier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted.

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

FEATURES

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Utilize with the nVent CADDY Wire Basket Tray C Bracket for multi-tier cable tray runs


Material: Steel
Finish: Electrogalvanized



SPECIFICATIONS

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Unit Weight
WBTLBRKT12		127 mm	41.4 mm	350.52mm	7.16 mm	0.712 kg
WBTLBRKT12BA	Black	127 mm	41.4 mm	198.12mm	7.16 mm	0.712 kg
WBTLBRKT4		127 mm	41.4 mm	96.52mm	7.16 mm	0.395 kg
WBTLBRKT4BA	Black	127 mm	41.4 mm	452.12mm	7.16 mm	0.395 kg
WBTLBRKT6		127 mm	41.4 mm	452.12mm	7.16 mm	0.476 kg
WBTLBRKT6BA	Black	127 mm	41.4 mm	502.92mm	7.16 mm	0.476 kg
WBTLBRKT8		127 mm	41.4 mm	553.72mm	7.16 mm	0.553 kg
WBTLBRKT8BA	Black	127 mm	41.4 mm	553.72mm	7.16 mm	0.553 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

