

M8x25mm Eye Bolt with 8.5mm Diameter Thru-Hole, electrogalvanized

CATALOG NUMBER

SLEBM8

FEATURES

Designed to accept nVent CADDY Speed Link wire rope or hook



PRODUCT ATTRIBUTES

Article Number: 195856

Material: Steel

Finish: Electrogalvanized

Screw Diameter (Sc): 8

Screw Length (L): 25mm

Hole Size (HS): 8.5 mm

Length (L): 50mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

