


Assembly Parts for Rugged Components



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

FEATURES

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

Product Family: EuropacPRO
Product Type: Assembly Kit



SPECIFICATIONS

Catalog Number	Type	Length	Package Quantity	Thread Size	Finish	Material	Works With
24566-100	Countersunk Screw	18mm	100	M4		Stainless Steel	Subracks
24566-101	Countersunk Screw	14mm	100	M4		Stainless Steel	Subracks
24560-140	Square Nut		100		Zinc Plated	Steel	Subracks
24566-102	Panhead Screw	14mm	100	M4		Stainless Steel	Subracks
24566-103	Panhead Screw	10mm	100	M4		Stainless Steel	Subracks
24566-104	Panhead Screw	8mm	100	M4		Stainless Steel	Subracks
24566-105	Countersunk Screw	7mm	100	M4		Stainless Steel	Subracks
24566-106	Countersunk Screw	10mm	100	M4		Stainless Steel	Subracks

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

