

Basic Plastic Conduit Clip



FEATURES

Push-in installation of conduit

Compatible with plastic Push-In Insert or with a simple screw to easily accommodate a variety of structures including concrete, brick, metal decks and plywood

Snap-together clips can be easily assembled to limit the number of fixing points to structure

Non-flame propagating per IEC 61386-25

Passed 650°C glowing/hot-wire test per EN 60695-2

Halogen free

UV-stabilized

Material: Polypropylene


Temperature: -10 to 85 °C

SPECIFICATIONS

Catalog Number	Article Number	Outer Diameter (OD)	A	B	C
SCBC16	800012	16 mm	21 mm	25 mm	18 mm
SCBC20	800013	20 mm	26 mm	29 mm	19 mm
SCBC25	800014	25 mm	32 mm	34 mm	22 mm
SCBC32	800015	32 mm	40 mm	41 mm	26 mm

Catalog Number	Article Number	Outer Diameter (OD)	A	B	C
SCBC40	800016	40 mm	50 mm	49 mm	30 mm
SCBC50	800017	50 mm	62 mm	59 mm	35 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

