

# Plastic Conduit Clip



## FEATURES

Push-in installation of conduit

Compatible with different structural attachment components to accommodate a variety of structures including concrete, brick, plywood, cable tray, spring steel fasteners and threaded rod

Snap-together clips can be easily assembled to limit the number of fixing points to structure

Non-flame propagating per IEC 61386-25

Passed 650°C glowing/hot-wire wire test per EN 60695-2

Halogen free

UV-stabilized

**Material:** Acrylonitrile Butadiene Styrene


**Temperature:** -10 to 80 °C

## SPECIFICATIONS

| Catalog Number | Article Number | Outer Diameter (OD) | A     | B     | C     |
|----------------|----------------|---------------------|-------|-------|-------|
| SCEC16HO       | 800000         | 16 mm               | 26 mm | 27 mm | 20 mm |
| SCEC20HO       | 800001         | 20 mm               | 30 mm | 31 mm | 22 mm |
| SCEC25HO       | 800002         | 25 mm               | 35 mm | 34 mm | 24 mm |
| SCEC32HO       | 800003         | 32 mm               | 43 mm | 39 mm | 28 mm |

| Catalog Number | Article Number | Outer Diameter (OD) | A     | B     | C     |
|----------------|----------------|---------------------|-------|-------|-------|
| SCEC40HO       | 800004         | 40 mm               | 54 mm | 45 mm | 32 mm |
| SCEC50HO       | 800005         | 50 mm               | 66 mm | 56 mm | 38 mm |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
 Option 1 – Customer Care  
 Option 2 – Technical Support

#### Europe

Netherlands:  
 +31 800-0200135  
 France:  
 +33 800 901 793

#### Europe

Germany:  
 800 1890272  
 Other Countries:  
 +31 13 5835404

#### APAC

Shanghai:  
 + 86 21 2412 1618/19  
 Sydney:  
 +61 2 9751 8500

