


# FPN Universal Anchor

## FEATURES

Expansion fixing for wood or drywall / plasterboard screws

For use in concrete, brick and lightweight concrete



**Material:** Nylon

**Static Load Safety Factor:** 5:1

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Screw Diameter | Length | Drill Bit Diameter | Drill Hole Depth | Static Load 1 |
|----------------|----------------|----------------|--------|--------------------|------------------|---------------|
| FPN10          | 570730         | 6 - 8 mm       | 50mm   | 10mm               | 60mm             | 1500N         |
| FPN12          | 570740         | 8 - 10 mm      | 60mm   | 12mm               | 70mm             | 1800N         |

Table 2/2

| Catalog Number | Article Number | Static Load 2 | Static Load 3 |
|----------------|----------------|---------------|---------------|
| FPN10          | 570730         | 850N          | 800N          |
| FPN12          | 570740         | 950N          | 800N          |

## ADDITIONAL PRODUCT DETAILS

Refer to Static Load 1 when anchoring in non-cracked concrete C20/25. Refer to Static Load 2 when anchoring in solid brick Mz 20. Refer to Static Load 3 when anchoring in solid sand-lime brick KS 20.

Static loads are calculated using the maximum Screw Diameter.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

