

# HD NI Heavy Duty Pipe Clamp, Fire/Sprinkler

## FEATURES

Fillet welded connector nut has flats to accommodate spanners



**Material:** Steel



## SPECIFICATIONS

Table 1/4

| Catalog Number | Article Number | Nut Included | Finish             | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|----------------|----------------|--------------|--------------------|---------------------|-------|---------------|
| HDN024HD       | 575002         | Yes          | Hot-Dip Galvanized | 20 - 24 mm          | 15    | M8, M10       |
| HDN030         | 577003         | Yes          | Electrogalvanized  | 25 - 30 mm          | 20    | M8, M10       |
| HDN035         | 577004         | Yes          | Electrogalvanized  | 31 - 35 mm          | 25    | M8, M10       |
| HDN045HD       | 575006         | Yes          | Hot-Dip Galvanized | 40 - 45 mm          | 32    | M8, M10       |
| HDN059         | 577008         | Yes          | Electrogalvanized  | 54 - 59 mm          |       | M8, M10       |
| HDN059HD       | 575008         | Yes          | Hot-Dip Galvanized | 54 - 59 mm          |       | M8, M10       |
| HDN102         | 577014         | Yes          | Electrogalvanized  | 95 - 102 mm         |       | M10, M12      |
| HDN108         | 577015         | Yes          | Electrogalvanized  | 102 - 108 mm        |       | M10, M12      |
| HDN129HD       | 575018         | Yes          | Hot-Dip Galvanized | 124 - 129 mm        |       | M10, M12      |
| HDN140         | 577019         | Yes          | Electrogalvanized  | 133 - 140 mm        |       | M10, M12      |
| HDN155         | 577021         | Yes          | Electrogalvanized  | 149 - 155 mm        |       | M12, M16      |

| Catalog Number | Article Number | Nut Included | Finish             | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|----------------|----------------|--------------|--------------------|---------------------|-------|---------------|
| HDN173         | 577023         | Yes          | Electrogalvanized  | 167 - 173 mm        | 150   | M12, M16      |
| HDN173HD       | 575023         | Yes          | Hot-Dip Galvanized | 167 - 173 mm        | 150   | M12, M16      |
| HDN182         | 577024         | Yes          | Electrogalvanized  | 176 - 182 mm        |       | M12, M16      |
| HDN205         | 577026         | Yes          | Electrogalvanized  | 199 - 205 mm        |       | M12, M16      |
| HDN216         | 577027         | Yes          | Electrogalvanized  | 207 - 216 mm        |       | M12, M16      |
| HDN226         | 577028         | Yes          | Electrogalvanized  | 219 - 226 mm        | 200   | M12, M16      |
| HDN226HD       | 575028         | Yes          | Hot-Dip Galvanized | 219 - 226 mm        | 200   | M12, M16      |
| HDN236         | 577029         | Yes          | Electrogalvanized  | 227 - 236 mm        |       | M16, M20      |
| HDN316         | 577068         | Yes          | Electrogalvanized  | 305 - 316 mm        |       | M16, M20      |

Table 2/4

| Catalog Number | Article Number | Nut Included | Finish            | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|----------------|----------------|--------------|-------------------|---------------------|-------|---------------|
| HDN020EG       | 579042         | Yes          | Electrogalvanized | 26 - 31 mm          | 20    | M8, M10       |
| HDN020G        | 579122         | Yes          | GEOMET® 321       | 26 - 31 mm          | 20    | M8, M10       |
| HDN025EG       | 579043         | Yes          | Electrogalvanized | 31 - 37 mm          |       | M8, M10       |
| HDN025G        | 579123         | Yes          | GEOMET® 321       | 31 - 37 mm          |       | M8, M10       |
| HDN032EG       | 579044         | Yes          | Electrogalvanized | 38 - 44 mm          | 32    | M8, M10       |
| HDN032G        | 579124         | Yes          | GEOMET® 321       | 38 - 44 mm          | 32    | M8, M10       |
| HDN040EG       | 579045         | Yes          | Electrogalvanized | 46 - 53 mm          | 40    | M8, M10       |
| HDN040G        | 579125         | Yes          | GEOMET® 321       | 46 - 53 mm          | 40    | M8, M10       |
| HDN047EG       | 579046         | Yes          | Electrogalvanized | 54 - 60 mm          |       | M8, M10       |
| HDN047G        | 579126         | Yes          | GEOMET® 321       | 54 - 60 mm          |       | M8, M10       |
| HDN050EG       | 579047         | Yes          | Electrogalvanized | 60 - 68 mm          | 50    | M8, M10       |
| HDN050G        | 579127         | Yes          | GEOMET® 321       | 60 - 68 mm          | 50    | M8, M10       |
| HDN060EG       | 579048         | Yes          | Electrogalvanized | 66 - 73 mm          |       | M8, M10       |
| HDN060G        | 579128         | Yes          | GEOMET® 321       | 66 - 73 mm          |       | M8, M10       |
| HDN065EG       | 579049         | Yes          | Electrogalvanized | 74 - 81 mm          | 65    | M10, M12      |
| HDN065G        | 579129         | Yes          | GEOMET® 321       | 74 - 81 mm          | 65    | M10, M12      |
| HDN075EG       | 579051         | Yes          | Electrogalvanized | 82 - 88 mm          |       | M10, M12      |
| HDN075G        | 579131         | Yes          | GEOMET® 321       | 82 - 88 mm          |       | M10, M12      |
| HDN080EG       | 579052         | Yes          | Electrogalvanized | 88 - 97 mm          | 80    | M10, M12      |
| HDN080G        | 579132         | Yes          | GEOMET® 321       | 88 - 97 mm          | 80    | M10, M12      |

Table 3/4

| Catalog Number | Article Number | Nut Included | Finish            | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|----------------|----------------|--------------|-------------------|---------------------|-------|---------------|
| HDN085EG       | 579053         | Yes          | Electrogalvanized | 93 - 100 mm         |       | M10, M12      |
| HDN085G        | 579133         | Yes          | GEOMET® 321       | 93 - 100 mm         |       | M10, M12      |
| HDN095EG       | 579054         | Yes          | Electrogalvanized | 101 - 109 mm        |       | M10, M12      |
| HDN095G        | 579134         | Yes          | GEOMET® 321       | 101 - 109 mm        |       | M10, M12      |
| HDN100EG       | 579055         | Yes          | Electrogalvanized | 110 - 118 mm        | 100   | M10, M12      |
| HDN100G        | 579135         | Yes          | GEOMET® 321       | 110 - 118 mm        | 100   | M10, M12      |
| HDN110EG       | 579056         | Yes          | Electrogalvanized | 116 - 126 mm        |       | M10, M12      |
| HDN110G        | 579136         | Yes          | GEOMET® 321       | 116 - 126 mm        |       | M10, M12      |
| HDN120EG       | 579057         | Yes          | Electrogalvanized | 130 - 141 mm        |       | M12, M16      |
| HDN120G        | 579137         | Yes          | GEOMET® 321       | 130 - 141 mm        |       | M12, M16      |
| HDN125EG       | 579058         | Yes          | Electrogalvanized | 136 - 147 mm        | 125   | M12, M16      |
| HDN125G        | 579138         | Yes          | GEOMET® 321       | 136 - 147 mm        | 125   | M12, M16      |
| HDN140EG       | 579059         | Yes          | Electrogalvanized | 144 - 154 mm        |       | M12, M16      |
| HDN140G        | 579139         | Yes          | GEOMET® 321       | 144 - 154 mm        |       | M12, M16      |
| HDN150EG       | 579061         | Yes          | Electrogalvanized | 160 - 169 mm        | 150   | M12, M16      |
| HDN150G        | 579141         | Yes          | GEOMET® 321       | 160 - 169 mm        | 150   | M12, M16      |
| HDN180EG       | 579062         | Yes          | Electrogalvanized | 170 - 180 mm        |       | M12, M16      |
| HDN180G        | 579142         | Yes          | GEOMET® 321       | 170 - 180 mm        |       | M12, M16      |
| HDN190EG       | 579063         | Yes          | Electrogalvanized | 202 - 214 mm        |       | M12, M16      |
| HDN190G        | 579143         | Yes          | GEOMET® 321       | 202 - 214 mm        |       | M12, M16      |

Table 4/4

| Catalog Number | Article Number | Nut Included | Finish            | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|----------------|----------------|--------------|-------------------|---------------------|-------|---------------|
| HDN200EG       | 579064         | Yes          | Electrogalvanized | 219 - 230 mm        | 200   | M12, M16      |
| HDN200G        | 579144         | Yes          | GEOMET® 321       | 219 - 230 mm        | 200   | M12, M16      |
| HDN250EG       | 579065         | Yes          | Electrogalvanized | 273 - 283 mm        | 250   | M20           |
| HDN250G        | 579145         | Yes          | GEOMET® 321       | 273 - 283 mm        | 250   | M20           |
| HDN300EG       | 579066         | Yes          | Electrogalvanized | 317 - 333 mm        | 300   | M20           |
| HDN300G        | 579146         | Yes          | GEOMET® 321       | 317 - 333 mm        | 300   | M20           |
| HDN350EG       | 579067         | Yes          | Electrogalvanized | 349 - 365 mm        | 350   | M20           |
| HDN350G        | 579147         | Yes          | GEOMET® 321       | 349 - 365 mm        | 350   | M20           |
| HDN400EG       | 579068         | Yes          | Electrogalvanized | 395 - 411 mm        | 400   | M20           |
| HDN400G        | 579148         | Yes          | GEOMET® 321       | 395 - 411 mm        | 400   | M20           |
| HDN450EG       | 579069         | Yes          | Electrogalvanized | 447 - 463 mm        | 450   | M20           |
| HDN450G        | 579149         | Yes          | GEOMET® 321       | 447 - 463 mm        | 450   | M20           |

| Catalog Number | Article Number | Nut Included | Finish            | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|----------------|----------------|--------------|-------------------|---------------------|-------|---------------|
| HDN500EG       | 579071         | Yes          | Electrogalvanized | 499 - 512 mm        | 500   | M20           |
| HDN500G        | 579151         | Yes          | GEOMET® 321       | 499 - 512 mm        | 500   | M20           |
| HDN015EG       | 579041         | Yes          | Electrogalvanized | 18 - 23 mm          | 15    | M8, M10       |
| HDN015G        | 579121         | Yes          | Electrogalvanized | 18 - 23 mm          | 15    | M8, M10       |

Table 1/4

| Catalog Number | Article Number | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|----------------|----------------|-----------|---------------|---------------------|----------------------------|------------------|
| HDN024HD       | 575002         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN030         | 577003         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN035         | 577004         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN045HD       | 575006         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN059         | 577008         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN059HD       | 575008         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN102         | 577014         | 30 mm     | 3 mm          | 8 mm                | M8                         | 40mm             |
| HDN108         | 577015         | 30 mm     | 3 mm          | 8 mm                | M8                         | 40mm             |
| HDN129HD       | 575018         | 30 mm     | 3 mm          | 8 mm                | M8                         | 40mm             |
| HDN140         | 577019         | 40 mm     | 4 mm          | 8 mm                | M8                         | 40mm             |
| HDN155         | 577021         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN173         | 577023         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN173HD       | 575023         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN182         | 577024         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN205         | 577026         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN216         | 577027         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN226         | 577028         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN226HD       | 575028         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN236         | 577029         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN316         | 577068         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |

Table 2/4

| Catalog Number | Article Number | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|----------------|----------------|-----------|---------------|---------------------|----------------------------|------------------|
| HDN020EG       | 579042         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN020G        | 579122         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN025EG       | 579043         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN025G        | 579123         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |

| Catalog Number | Article Number | Width(W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|----------------|----------------|----------|---------------|---------------------|----------------------------|------------------|
| HDN032EG       | 579044         | 25 mm    | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN032G        | 579124         | 25 mm    | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN040EG       | 579045         | 25 mm    | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN040G        | 579125         | 25 mm    | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN047EG       | 579046         | 25 mm    | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN047G        | 579126         | 25 mm    | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN050EG       | 579047         | 25 mm    | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN050G        | 579127         | 25 mm    | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN060EG       | 579048         | 25 mm    | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN060G        | 579128         | 25 mm    | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN065EG       | 579049         | 30 mm    | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN065G        | 579129         | 30 mm    | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN075EG       | 579051         | 30 mm    | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN075G        | 579131         | 30 mm    | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN080EG       | 579052         | 30 mm    | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN080G        | 579132         | 30 mm    | 3 mm          | 8 mm                | M8                         | 25mm             |

Table 3/4

| Catalog Number | Article Number | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|----------------|----------------|-----------|---------------|---------------------|----------------------------|------------------|
| HDN085EG       | 579053         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN085G        | 579133         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN095EG       | 579054         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN095G        | 579134         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN100EG       | 579055         | 30 mm     | 3 mm          | 10 mm               | M10                        | 40mm             |
| HDN100G        | 579135         | 30 mm     | 3 mm          | 10 mm               | M10                        | 40mm             |
| HDN110EG       | 579056         | 30 mm     | 3 mm          | 10 mm               | M10                        | 40mm             |
| HDN110G        | 579136         | 30 mm     | 3 mm          | 10 mm               | M10                        | 40mm             |
| HDN120EG       | 579057         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN120G        | 579137         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN125EG       | 579058         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN125G        | 579138         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN140EG       | 579059         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN140G        | 579139         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN150EG       | 579061         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |

| Catalog Number | Article Number | Width(W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|----------------|----------------|----------|---------------|---------------------|----------------------------|------------------|
| HDN150G        | 579141         | 40 mm    | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN180EG       | 579062         | 40 mm    | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN180G        | 579142         | 40 mm    | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN190EG       | 579063         | 40 mm    | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN190G        | 579143         | 40 mm    | 4 mm          | 12 mm               | M12                        | 40mm             |

Table 4/4

| Catalog Number | Article Number | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|----------------|----------------|-----------|---------------|---------------------|----------------------------|------------------|
| HDN200EG       | 579064         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN200G        | 579144         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN250EG       | 579065         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN250G        | 579145         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN300EG       | 579066         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN300G        | 579146         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN350EG       | 579067         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN350G        | 579147         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN400EG       | 579068         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN400G        | 579148         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN450EG       | 579069         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN450G        | 579149         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN500EG       | 579071         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN500G        | 579151         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN015EG       | 579041         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN015G        | 579121         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |

Table 1/4

| Catalog Number | Article Number | Static Load | Certifications                                              |
|----------------|----------------|-------------|-------------------------------------------------------------|
| HDN024HD       | 575002         | 2000N       |                                                             |
| HDN030         | 577003         | 2000N       | VdS G4090030, FM Approved, Pipe Hanger Components, ITB      |
| HDN035         | 577004         | 2000N       | FM Approved, Pipe Hanger Components, VdS G4090030, ITB      |
| HDN045HD       | 575006         | 2000N       | VdS G4090030, FM Approved, Pipe Hanger Components           |
| HDN059         | 577008         | 2000N       | VdS G4090030, ITB                                           |
| HDN059HD       | 575008         | 2000N       | VdS G4090030                                                |
| HDN102         | 577014         | 3500N       | AON Fire Protection, BB019, pipe hangers, VdS G4090030, ITB |

| Catalog Number | Article Number | Static Load | Certifications                                                                                   |
|----------------|----------------|-------------|--------------------------------------------------------------------------------------------------|
| HDN108         | 577015         | 3500N       | VdS G4090030, ITB, AON Fire Protection, BB019, pipe hangers                                      |
| HDN129HD       | 575018         | 5000N       | VdS G4090030                                                                                     |
| HDN140         | 577019         | 5000N       | ITB, AON Fire Protection, BB019, pipe hangers, VdS G4090030                                      |
| HDN155         | 577021         | 5000N       | ITB, AON Fire Protection, BB019, pipe hangers, VdS G4090030                                      |
| HDN173         | 577023         | 5000N       | AON Fire Protection, BB019, pipe hangers, FM Approved, Pipe Hanger Components, VdS G4090030, ITB |
| HDN173HD       | 575023         | 5000N       | FM Approved, Pipe Hanger Components, VdS G4090030                                                |
| HDN182         | 577024         | 8500N       | ITB                                                                                              |
| HDN205         | 577026         | 8500N       | ITB                                                                                              |
| HDN216         | 577027         | 8500N       | ITB                                                                                              |
| HDN226         | 577028         | 8500N       | ITB, VdS G4090030                                                                                |
| HDN226HD       | 575028         | 8500N       | VdS G4090030                                                                                     |
| HDN236         | 577029         | 10000N      | ITB                                                                                              |
| HDN316         | 577068         | 10000N      | ITB                                                                                              |

Table 2/4

| Catalog Number | Article Number | Static Load | Certifications                      |
|----------------|----------------|-------------|-------------------------------------|
| HDN020EG       | 579042         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN020G        | 579122         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN025EG       | 579043         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN025G        | 579123         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN032EG       | 579044         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN032G        | 579124         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN040EG       | 579045         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN040G        | 579125         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN047EG       | 579046         | 2000N       |                                     |
| HDN047G        | 579126         | 2000N       |                                     |
| HDN050EG       | 579047         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN050G        | 579127         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN060EG       | 579048         | 3500N       |                                     |
| HDN060G        | 579128         | 3500N       |                                     |
| HDN065EG       | 579049         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN065G        | 579129         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN075EG       | 579051         | 3500N       |                                     |
| HDN075G        | 579131         | 3500N       |                                     |

| Catalog Number | Article Number | Static Load | Certifications                      |
|----------------|----------------|-------------|-------------------------------------|
| HDN080EG       | 579052         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN080G        | 579132         | 3500N       | FM Approved, Pipe Hanger Components |

Table 3/4


| Catalog Number | Article Number | Static Load | Certifications                      |
|----------------|----------------|-------------|-------------------------------------|
| HDN085EG       | 579053         | 3500N       |                                     |
| HDN085G        | 579133         | 3500N       |                                     |
| HDN095EG       | 579054         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN095G        | 579134         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN100EG       | 579055         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN100G        | 579135         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN110EG       | 579056         | 5000N       |                                     |
| HDN110G        | 579136         | 5000N       |                                     |
| HDN120EG       | 579057         | 5000N       |                                     |
| HDN120G        | 579137         | 5000N       |                                     |
| HDN125EG       | 579058         | 5000N       | FM Approved, Pipe Hanger Components |
| HDN125G        | 579138         | 5000N       | FM Approved, Pipe Hanger Components |
| HDN140EG       | 579059         | 5000N       |                                     |
| HDN140G        | 579139         | 5000N       |                                     |
| HDN150EG       | 579061         | 5000N       | FM Approved, Pipe Hanger Components |
| HDN150G        | 579141         | 5000N       | FM Approved, Pipe Hanger Components |
| HDN180EG       | 579062         | 8500N       |                                     |
| HDN180G        | 579142         | 8500N       |                                     |
| HDN190EG       | 579063         | 8500N       |                                     |
| HDN190G        | 579143         | 8500N       |                                     |

Table 4/4

| Catalog Number | Article Number | Static Load | Certifications |
|----------------|----------------|-------------|----------------|
| HDN200EG       | 579064         | 8500N       |                |
| HDN200G        | 579144         | 8500N       |                |
| HDN250EG       | 579065         | 10000N      |                |
| HDN250G        | 579145         | 10000N      |                |
| HDN300EG       | 579066         | 12500N      |                |
| HDN300G        | 579146         | 12500N      |                |
| HDN350EG       | 579067         | 12500N      |                |
| HDN350G        | 579147         | 12500N      |                |

| Catalog Number | Article Number | Static Load | Certifications |
|----------------|----------------|-------------|----------------|
| HDN400EG       | 579068         | 12500N      |                |
| HDN400G        | 579148         | 12500N      |                |
| HDN450EG       | 579069         | 12500N      |                |
| HDN450G        | 579149         | 12500N      |                |
| HDN500EG       | 579071         | 12500N      |                |
| HDN500G        | 579151         | 12500N      |                |
| HDN015EG       | 579041         | 2000N       |                |
| HDN015G        | 579121         | 2000N       |                |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

