

SC Cable Snap Clip



FEATURES

Easily supports cable and plastic conduit from flanges

Requires only a hammer to install


Material: Spring Steel
Finish: nVent CADDY Armour

SPECIFICATIONS

Catalog Number	Article Number	Flange Thickness (FT)	Outer Diameter (OD)	Thickness (T)
24SC1214R25	191002	2 - 4 mm	12 - 14 mm	0.6 mm
24SC1518R25	191003	2 - 4 mm	15 - 18 mm	0.6 mm
24SC1924	187610	2 - 4 mm	19 - 24 mm	0.6 mm
24SC1924R25	191004	2 - 4 mm	19 - 24 mm	0.6 mm
24SC2530	187630	2 - 4 mm	25 - 30 mm	0.6 mm
24SC2530R25	191005	2 - 4 mm	25 - 30 mm	0.6 mm
24SC89	187530	2 - 4 mm	8 - 9 mm	0.6 mm
47SC1518	187580	4 - 7 mm	15 - 18 mm	0.6 mm
47SC1518R25	191009	4 - 7 mm	15 - 18 mm	0.6 mm
47SC1924	187600	4 - 7 mm	19 - 24 mm	0.6 mm
47SC1924R25	191010	4 - 7 mm	19 - 24 mm	0.6 mm
47SC2530	187620	4 - 7 mm	25 - 30 mm	0.6 mm
47SC2530R25	191011	4 - 7 mm	25 - 30 mm	0.6 mm

Catalog Number	Article Number	Flange Thickness (FT)	Outer Diameter (OD)	Thickness (T)
47SC89	187520	4 - 7 mm	8 - 9 mm	0.6 mm
812SC1518R25	191015	8 - 12 mm	15 - 18 mm	0.6 mm
812SC1924	187690	8 - 12 mm	19 - 24 mm	0.6 mm
812SC1924R25	191016	8 - 12 mm	19 - 24 mm	0.6 mm
812SC2530	187700	8 - 12 mm	25 - 30 mm	0.6 mm
812SC2530R25	191017	8 - 12 mm	25 - 30 mm	0.6 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/GRDDT

