


Speedway Cable Ladder Flat Elbow, 90°



FEATURES

Creates a 90° corner change in cable tray direction

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant


Responsive design and layout services, including seismic

Material: Steel
Finish: Hot-Dip Galvanized



SPECIFICATIONS

Catalog Number	Article Number	Width (W)	Angle (a)	A	B	C
CL110X150FE90HD	840200	150 mm	90 °	545 mm	545 mm	80 mm
CL110X300FE90HD	840210	300 mm	90 °	695 mm	695 mm	80 mm
CL110X450FE90HD	840220	450 mm	90 °	845 mm	845 mm	80 mm
CL110X600FE90HD	840230	600 mm	90 °	995 mm	995 mm	80 mm
CL110X750FE90HD	840240	750 mm	90 °	1145 mm	1145 mm	80 mm
CL110X900FE90HD	840250	900 mm	90 °	1295 mm	1295 mm	80 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

