

# 510 nVent CADDY EZ Riser



The 510 nVent CADDY EZ Riser is a quick-closing pipe clamp, ideal for supporting vertical steel pipe where space is available. Ready-to-use out of the box, this solution has slotted holes to simplify assembly and eliminate loose hardware. Due to the serrated washer-head design, installers can easily assemble the EZ Riser with just a single tool.

## FEATURES

Only one tool needed to tighten due to serrated washer-heads

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

**Material:** Steel  
**Finish:** Electrogalvanized



## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | NB/DN | Outer Diameter (OD) | Hole Size (HS) | A      | B     |
|----------------|----------------|-------|---------------------|----------------|--------|-------|
| 5100800EG      | 179336         | 200   | 219 mm              | 17 mm          | 464 mm | 51 mm |
| 5101000EG      | 179337         | 250   | 273 mm              | 17 mm          | 524 mm | 51 mm |
| 5101200EG      | 179338         | 300   | 324 mm              | 17 mm          | 569 mm | 51 mm |

Table 2/2



| Catalog Number | Article Number | Static Load | Certifications |
|----------------|----------------|-------------|----------------|
| 5100800EG      | 179336         | 11100N      | cUL, UL        |
| 5101000EG      | 179337         | 11100N      |                |
| 5101200EG      | 179338         | 12000N      |                |

## ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Slotted holes and bolts for pipe sizes up to 12" only.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

