

# RatiopacPRO Complete Desktop Case, Shielded



The nVent SCHROFF RatiopacPRO case with EMC shielding, provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides a sleek design for desktop applications.

## FEATURES

Desktop enclosure with pre-configured components, in accordance to IEC 60297-3-101; prepared for 19" components, e.g. plug-in units and euroboards

Shielded

Version with cover strips

Ventilation slit in base plate

Rear panel perforated

Conforms with DIN EN 62368-1

- EMC Shielding: Yes
- Product Family: RatiopacPRO
- Product Type: Case
- Static Load: 25kg
- Type: Case for 19" Components



## SPECIFICATIONS

| Table 1/3      |             |            |         |                  |               |              |
|----------------|-------------|------------|---------|------------------|---------------|--------------|
| Catalog Number | Rack Height | Rack Width | Depth   | Package Quantity | Usable Height | Usable Width |
| 24572-050      | 3U          | 28HP       | 255.5mm | 1                | 112.3mm       | 148mm        |
| 24572-051      | 3U          | 42HP       | 255.5mm | 1                | 112.3mm       | 219mm        |
| 24572-052      | 3U          | 42HP       | 315.5mm | 1                | 112.3mm       | 219mm        |
| 24572-053      | 3U          | 63HP       | 315.5mm | 1                | 112.3mm       | 326mm        |

| Catalog Number | Rack Height | Rack Width | Depth   | Package Quantity | Usable Height | Usable Width |
|----------------|-------------|------------|---------|------------------|---------------|--------------|
| 24572-054      | 3U          | 84HP       | 315.5mm | 1                | 112.3mm       | 432mm        |
| 24572-055      | 3U          | 84HP       | 375.5mm | 1                | 112.3mm       | 432mm        |
| 24572-056      | 3U          | 84HP       | 435.5mm | 1                | 112.3mm       | 432mm        |
| 24572-064      | 6U          | 42HP       | 315.5mm | 1                | 245.7mm       | 219mm        |
| 24572-065      | 6U          | 63HP       | 315.5mm | 1                | 245.7mm       | 326mm        |
| 24572-066      | 6U          | 84HP       | 315.5mm | 1                | 245.7mm       | 432mm        |
| 24572-067      | 6U          | 84HP       | 375.5mm | 1                | 245.7mm       | 432mm        |
| 24572-068      | 6U          | 84HP       | 435.5mm | 1                | 245.7mm       | 432mm        |

| Table 2/3      |                             |                |                                                                           |                           |        |          |
|----------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|--------|----------|
| Catalog Number | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height | Material |
| 24572-050      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6m | Aluminum |
| 24572-051      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6m | Aluminum |
| 24572-052      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6m | Aluminum |
| 24572-053      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6m | Aluminum |
| 24572-054      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6m | Aluminum |
| 24572-055      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6m | Aluminum |
| 24572-056      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 132.6m | Aluminum |
| 24572-064      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9m | Aluminum |
| 24572-065      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9m | Aluminum |
| 24572-066      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9m | Aluminum |

| Catalog Number | Front Frame Construction    | Cooling Option | Complies With                                                             | Finish                    | Height  | Material |
|----------------|-----------------------------|----------------|---------------------------------------------------------------------------|---------------------------|---------|----------|
| 24572-067      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |
| 24572-068      | Side Trim, Horizontal Rails | No             | IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11 | Passivated, Powder Coated | 265.9mm | Aluminum |

| Table 3/3      |                   |         |
|----------------|-------------------|---------|
| Catalog Number | Protection Rating | Width   |
| 24572-050      | IP20              | 164.4mm |
| 24572-051      | IP20              | 235.5mm |
| 24572-052      | IP20              | 235.5mm |
| 24572-053      | IP20              | 342.4mm |
| 24572-054      | IP20              | 448.9mm |
| 24572-055      | IP20              | 448.9mm |
| 24572-056      | IP20              | 448.9mm |
| 24572-064      | IP20              | 235.5mm |
| 24572-065      | IP20              | 342.4mm |
| 24572-066      | IP20              | 448.9mm |
| 24572-067      | IP20              | 448.9mm |
| 24572-068      | IP20              | 448.9mm |

## ADDITIONAL PRODUCT DETAILS

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

