



		ΔR^2 can be simplified	ΔR^2 combination not recommended
Length $\neq L$		-	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Horizontal and vertical		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$		+	+
Length $\neq L$		+	+
Area $\neq A$			

34566-228

FEATURES

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings



Rack Width: 28HP

Package Quantity: 1

Finish: Anodized

Length: 147.32mm

Material: Aluminum

Product Family: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, KD

Works With: Subracks

Gross Weight: 0.09kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

Without M4 thread to front, without printing and without notch for 19" bracket.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

