

# nVent CADDY Cat 425 Adjustable Cable Support



## FEATURES

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Simple unlocking and locking of bar allows for additional cables to be added easily after installation

Adjustable strap allows for multiple support sizes to reduce inventory

Cost effective alternative to expensive cable tray

cULus® Listed and complies with NEC® and TIA requirements for structured cabling systems

Suitable for air handling spaces (plenum)

**Material:** Steel;Polyethylene

**Finish:** Electrogalvanized




## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Diameter (Ø)   | Area               | Cable Capacity, Cat 5e | Cable Capacity, Cat 6 | Cable Capacity, Cat 6A |
|----------------|----------------|----------------|--------------------|------------------------|-----------------------|------------------------|
| CAT425         | 181130         | 100 mm, 150 mm | 518mm <sup>2</sup> | 425                    | 325                   | 210                    |
| CAT425A6       |                | 100 mm, 150 mm | 518mm <sup>2</sup> | 425                    | 325                   | 210                    |

| Table 2/2      |                |                |             |                |
|----------------|----------------|----------------|-------------|----------------|
| Catalog Number | Article Number | Hole Size (HS) | Static Load | Certifications |
| CAT425         | 181130         | 7 mm           | 450N        | UL, ITB, cUL   |
| CAT425A6       |                | 9.5 mm         | 450N        | UL, cUL        |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

