


SCH2 Single Piece Strut Clamp for Cable/Conduit



FEATURES

One-piece cable/conduit clamp with protective boot

No screws or bolts to drop

Requires only a screwdriver or nutdriver for installation

Fits into open side of strut channel

FM® Specification Tested (from 1/2" to 4" of EMT Conduit Size)

Material: Steel
Finish: Electrogalvanized




SPECIFICATIONS

Catalog Number	Outer Diameter (OD)	Static Load 1 (F1)	Ultimate Static Load 2 (F2)	Ultimate Static Load 3 (F3)	Certifications
SCH12B	14.5 - 23.4 mm	880N	334N	222N	UL, OSHPD/HCAI, cUL
SCH16B	18.3 - 29.5 mm	880N	334N	222N	cUL, UL, OSHPD/HCAI
SCH20B	25.4 - 38.4 mm	880N	334N	222N	cUL, UL, OSHPD/HCAI
SCH24B	31.8 - 44.2 mm	1550N	334N	222N	cUL, UL, OSHPD/HCAI
SCH32B	44.2 - 55.9 mm	1550N	334N	222N	UL, OSHPD/HCAI, cUL
SCH40B	50.8 - 60.5 mm	1550N	334N	222N	OSHPD/HCAI, cUL, UL

Catalog Number	Outer Diameter (OD)	Static Load 1 (F1)	Ultimate Static Load2 (F2)	Ultimate Static Load3 (F3)	Certifications
SCH48B	60.5 - 73.2 mm	1550N	334N	222N	OSHDPD/HCAI, cUL, UL
SCH56B	69.1 - 88.9 mm	1550N	334N	222N	OSHDPD/HCAI, cUL, UL
SCH64B	82.6 - 101.6 mm	1550N	334N	222N	OSHDPD/HCAI, cUL, UL
SCH72B	97.8 - 114.3 mm	1550N	334N	222N	UL, cUL, OSHDPD/HCAI
SCH8B	8.6 - 18 mm	880N	334N	222N	cUL, UL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

