


# Wire Basket Tray C Bracket



Engineered for efficiency and adaptability, the nVent CADDY Wire Basket Tray C Bracket is a fast and simple component of modern cable management systems. Designed to streamline installation processes, this bracket excels in both hard-ceiling and two-tier wall mounting scenarios, offering contractors a reliable and time-saving solution for complex environments.

The C Bracket ensures that high-performance, low-voltage and data cables are securely supported with minimal effort. Simply pair with the nVent CADDY Wire Basket Tray Washer Support or nVent CADDY Wire Basket Tray Ground Splice and quickly fasten it to the wire basket tray to create a robust framework for layered tray runs. This combination not only enhances structural integrity but also provides the flexibility needed for multi-tiered installations, accommodating evolving infrastructure demands without compromising safety or performance.

## FEATURES

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Side load access for cable installation

Ideal for ceiling, wall and channel installations

Side load access for simple cable installation

**Material:** Steel  
**Finish:** Electrogalvanized




## SPECIFICATIONS

| Catalog Number | Color | Height (H) | Width (W) | Length (L) | Length 1 (L1) | Hole Size (HS) | Unit Weight |
|----------------|-------|------------|-----------|------------|---------------|----------------|-------------|
| WBTCBRKT12     |       | 200.03 mm  | 41.4 mm   | 350.52mm   | 139.7 mm      | 7.137 mm       | 1.025 kg    |
| WBTCBRKT12BA   | Black | 200.03 mm  | 41.4 mm   | 350.52mm   | 139.7 mm      | 7.137 mm       | 1.025 kg    |
| WBTCBRKT18     |       | 200.03 mm  | 41.4 mm   | 499.11mm   | 139.7 mm      | 7.137 mm       | 1.27 kg     |
| WBTCBRKT18BA   | Black | 200.03 mm  | 41.4 mm   | 499.11mm   | 139.7 mm      | 7.137 mm       | 1.27 kg     |
| WBTCBRKT4      |       | 200.03 mm  | 41.4 mm   | 151.917mm  | 139.7 mm      | 7.137 mm       | 0.708 kg    |

| Catalog Number | Color | Height (H) | Width (W) | Length (L) | Length 1 (L1) | Hole Size (HS) | Unit Weight |
|----------------|-------|------------|-----------|------------|---------------|----------------|-------------|
| WBTCBRKT4BA    | Black | 200.03 mm  | 41.4 mm   | 151.917mm  | 139.7 mm      | 7.137 mm       | 0.708 kg    |
| WBTCBRKT6      |       | 200.03 mm  | 41.4 mm   | 201.93mm   | 139.7 mm      | 7.137 mm       | 0.789 kg    |
| WBTCBRKT6BA    | Black | 200.03 mm  | 41.4 mm   | 201.93mm   | 139.7 mm      | 7.137 mm       | 0.789 kg    |
| WBTCBRKT8      |       | 200.03 mm  | 41.4 mm   | 251.46mm   | 139.7 mm      | 7.137 mm       | 0.866 kg    |
| WBTCBRKT8BA    | Black | 200.03 mm  | 41.4 mm   | 251.46mm   | 139.7 mm      | 7.137 mm       | 0.866 kg    |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

