

# PMC Mezzanine Front Panel, Untreated, With EMC Shielding



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments. For O-ring EMC gasket.

## FEATURES

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

**EMC Shielding:** Yes  
**Product Type:** Front Panel  
**Type:** Front Panel without Handle



## SPECIFICATIONS

Table 1/2

| Catalog Number | Package Quantity | Accessory Type | Mounting       | Gasket Type | Front Finish  | Rear Finish   |
|----------------|------------------|----------------|----------------|-------------|---------------|---------------|
| 20835-598      | 1                | Front panel    | Screw-on Front | O-Ring EMC  | Anodized      | Conductive    |
| 20835-889      | 1                | Front panel    | Screw-on Front | O-Ring EMC  | Anodized      | Conductive    |
| 20835-890      | 1                |                | Screw-on Front |             |               |               |
| 20835-893      | 10               |                | Screw-on Front |             | Chrome Plated | Chrome Plated |
| 20835-922      | 1                |                | Screw-on Front |             | Chrome Plated | Chrome Plated |
| 20835-923      | 1                |                | Screw-on Front |             | Chrome Plated | Chrome Plated |
| 20835-924      | 10               |                | Screw-on Front |             | Chrome Plated | Chrome Plated |
| 20835-928      | 10               |                | Screw-on Front |             | Anodized      | Conductive    |

Table 2/2

| Catalog Number | Treated Edges | Complies With             | Depth | Finish   | Height | Material | Width  |
|----------------|---------------|---------------------------|-------|----------|--------|----------|--------|
| 20835-598      | No            | PMC Mezzanine, IEEE P1386 | 2.5mm | Anodized | 74mm   | Aluminum | 12.7mm |

| Catalog Number | Treated Edges | Complies With             | Depth | Finish   | Height | Material | Width  |
|----------------|---------------|---------------------------|-------|----------|--------|----------|--------|
| 20835-889      | No            | PMC Mezzanine, IEEE P1386 | 2.5mm | Anodized | 74mm   | Aluminum | 12.7mm |
| 20835-890      | No            | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |
| 20835-893      | Yes           | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |
| 20835-922      | Yes           | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |
| 20835-923      | Yes           | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |
| 20835-924      | Yes           | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |
| 20835-928      | No            | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.