

BC-MSM Conduit to Beam Clamp, Side Mount



FEATURES

Easy installation to beam flanges

Eliminates offset bending conduit


Conduit clip rotates 360 degrees

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS

Catalog Number	Article Number	E-Number	Outer Diameter (OD)	Flange Thickness (FT)	Torque (TQ)	Static Load	Certifications
EBC16MSM	172660		23.4 - 35 mm	16 mm Max	3 N·m	110N	ITB
EBC20MSM	172670	1319455	35 - 42 mm	16 mm Max	3 N·m	110N	ITB
EBC24MSM	172680		42 - 50 mm	16 mm Max	3 N·m	110N	ITB
EBC32MSM	172690		50 - 60 mm	16 mm Max	3 N·m	110N	ITB
EBC6MSM	172650		14 - 18 mm	16 mm Max	3 N·m	110N	
EBC812MSM	160180	1319403	18 - 30 mm	16 mm Max	3 N·m	110N	ITB



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

