

Bolt Close Conduit/Pipe Clamp



FEATURES

Retained bolt and built-in nut means there are less parts to handle or drop

Combo head bolt works with slotted, hex, #3 phillips or #2 robertson drivers



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Nut Type	Outer Diameter (OD)
CD1B	181190	1340310	Steel	Electrogalvanized	Built-In Nut	19 - 25 mm

Table 2/2

Catalog Number	Article Number	E-Number	Hole Size (HS)	Static Load 1 (F1)	Static Load 2 (F2)
CD1B	181190	1340310	7.14 mm	880N	220N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

