

C-ES Cable to Vertical Flange Clamp



FEATURES

Supports single run of cable

Attaches to beam flanges, angle iron, joists and other structural supports

Material: Steel
Finish: Hot-Dip Galvanized

SPECIFICATIONS



Catalog Number	Article Number	E-Number	Outer Diameter (OD)	A	Torque (TQ)
C12ES	337000	1341235	6 - 12 mm	43 mm	2 N·m
C16ES	337010	1341236	12 - 16 mm	43 mm	2 N·m
C20ES	337020	1341237	16 - 20 mm	43 mm	2 N·m
C24ES	337030	1341238	20 - 24 mm	43 mm	2 N·m
C28ES	337040	1341239	24 - 28 mm	43 mm	2 N·m
C32ES	337050	1341240	28 - 32 mm	43 mm	2 N·m
C36ES	337060	1341241	32 - 36 mm	43 mm	2 N·m
C40ES	337070	1341242	36 - 40 mm	43 mm	2 N·m
C44ES	337080	1341243	40 - 44 mm	43 mm	4 N·m
C48ES	337090	1341244	44 - 48 mm	43 mm	4 N·m
C52ES	337100	1341245	48 - 52 mm	43 mm	4 N·m
C56ES	337110	1341246	52 - 56 mm	43 mm	4 N·m
C60ES	337120	1341247	56 - 60 mm	43 mm	4 N·m

Catalog Number	Article Number	E-Number	Outer Diameter (OD)	A	Torque (TQ)
C64ES	337130	1341248	60 - 64 mm	43 mm	4 N·m

ADDITIONAL PRODUCT DETAILS

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

