


Cantilever Arm with E4 Channel



FEATURES

Perforated, cold rolled

Slotted backplate

Material: Steel
Finish: Electrogalvanized



SPECIFICATIONS

Catalog Number	Article Number	E-Number	Length (L)
CE420H0200EG	599935		200mm
CE420H0300EG	599950	3436018	300mm
CE420H0350EG	599960		350mm
CE420H0450EG	599970	3436019	450mm
CE420H0550EG	599980	1319930	550mm
CE420H0650EG	599990	1319931	650mm
CE420H0800EG	599995		800mm

Height (H): 120 mm

Width (W): 40 mm

Thickness (T): 2 mm

A: 40 mm


B: 38 mm

C: 15.5 mm

D: 50 mm

E: 6 mm
X: 11 x 18 mm
Y: 14 x 27 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America	Europe	Europe	APAC
+1.800.753.9221	Netherlands:	Germany:	Shanghai:
Option 1 – Customer Care	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
Option 2 – Technical	France:	Other Countries:	Sydney:
Support	+33 800 901 793	+31 13 5835404	+61 2 9751 8500

